

80-Column Black and White Dot-Matrix Printer



The 80-column black and white dot-matrix printer can be used as an I/A Series® system log or alarm printer.

FEATURES

- ▶ Produces high-quality black/white hard copy output from I/A Series® Windows® based workstations
- ▶ Can be used to reliably print black text in alarm or message logs
- ▶ Quiet operation.

OVERVIEW

The 80-column color dot-matrix printer is desk- or table-mounted, and can be used as a log or alarm printer for black/white text applications. It connects to a workstation via either a USB cable or via a supported Ethernet network.

FUNCTIONAL SPECIFICATIONS

Print Characteristics

PRINT SPEED FOR 10 CHARACTER PER INCH SETTING

Letter Mode

95 characters per second

Utility Mode

380 characters per second

PRINT HEAD

24 pins

GRAPHICS RESOLUTION

240 (H) x 216 (V) dpi maximum

EMULATION

Epson® FX, IBM® ProPrinter®, OKI MICROLINE

Paper

TYPE

Single-part, multi-part, continuous forms, and cutsheet

PAPER FEEDING

Rear Push and Friction Feed

OPTIONS

Bottom push tractor, top pull tractor, cutsheet feeder, roll paper stand

Operating Systems Supported

Windows® 7, Windows XP, Windows 2000

Memory

128K

Data Transmission

INTERFACE TYPES

IEEE Parallel and USB on all models; also available with RS-232C Serial or OkiLAN® 10/100Base-T Internal Print Server standard

Part Numbers

- ▶ P0928FR: 120 V ac OKI Data MICROLINE® 420 80-Column Dot Matrix B&W Network/USB Printer.
- ▶ P0928FS: 230 V ac OKI Data MICROLINE® 420 80-Column Dot Matrix B&W Network/USB Printer.

ENVIRONMENTAL SPECIFICATIONS

Power Requirements

LINE VOLTAGE

P0928FR: 100 V ac -10% ~ 127 V ac +10%

P0928FS: 220 V ac -10% ~ 240 V ac +10%

LINE FREQUENCY

50 or 60 Hz

Location

UL/UL-C listed as suitable for use in ordinary locations and meets ordinary safety standards for fire and shock hazards.

Contamination

Class G1 (Mild) as defined in ISA Standard S71.04

PHYSICAL SPECIFICATIONS

Width x Depth x Height

17.1" x 21.5" x 15.3"
(435 mm x 547 mm x 389 mm)

Mass

13 lb (5.9 kg)

Cable for Local Connections

USB A/B cable - P0972SN (1.8 m (6 ft))

Mounting

Table or desk

DIMENSIONS—NOMINAL

mm
in



