


# I/A Series® Remote Terminal Unit (RTU)

## RTU 20 – 16 Permanent Digital Output Module



The 16 Permanent Digital Output module is a full-size electronic board in the I/A Series RTU 20 designed to drive 16 steady digital outputs through voltage-free bistable relay contacts.

Field devices can be directly driven by on-board relays with gold-plated output contacts and an expected lifecycle of  $10^7$  operations. Each relay provides a 1500 Vrms coil contacts isolation.


Four outputs have SPDT (single-pole, double-throw: Common + NO + NC) contacts, while the other twelve are SPST (single-pole, single-throw: Common + NO).

When the SCADA master station transmits a control output message to the RTU, the output relay activation can be executed immediately or after a “check-back” validity verification (with a 12-second time-out between the “select/check” and “operate” messages).

The module can be programmed to set the output contacts in “reset condition” or “hold last state” mode at power-up.

Several LEDs, located on the module’s front edge, provide local fault indication and digital output status (one LED for each output), while an optional alphanumeric LCD display (mounted on the RTU cabinet) can monitor the module status, on request.

16 PERMANENT DIGITAL OUTPUT MODULE – BLOCK DIAGRAM



SPECIFICATIONS

<b>Outputs</b> 16 steady voltage-free contacts	<b>Maximum Switching Capacity (UL/CSA Rating)</b> dc ONLY 60 W, 48 V
<b>Maximum Power Requirements</b> +5 V dc/16 mA, +12 V dc/25 mA (on relay activation)	<b>Operating Temperature</b> –25°C to +70°C
<b>Isolation Voltage</b> 1500 Vrms (relay coil contacts), 1000 Vrms (contact-contact)	<b>Field Cable Connection</b> Removable screw-terminal blocks on dedicated terminal board connected to module's backplane
<b>Relay Specification</b> Expected lifecycle: 10 <sup>7</sup> operations, gold-plated contacts	<b>Diagnostics and Status</b> LED indicators on module's front edge
<b>Maximum Load (UL/CSA Rating)</b> 2 A at 30 V dc	



**The Foxboro Company**

33 Commercial Street

Foxboro, Massachusetts 02035-2099

United States of America

<http://www.foxboro.com>

Inside U.S.: 1-508-543-8750 or 1-888-FOXBORO (1-888-369-2676)

Outside U.S.: Contact your local Foxboro representative.

Foxboro and I/A Series are registered trademarks of The Foxboro Company.

Invensys is a trademark of Invensys plc.

All other brand names may be trademarks of their respective companies.

Copyright 2001 The Foxboro Company

All rights reserved