


## **I/A Series® Remote Terminal Unit (RTU)**

### **RTU 20 – 8 Momentary Digital Output Module**



The 8 Momentary Digital Output module is a half-size electronic board in the I/A Series RTU 20 designed to drive 8 digital outputs through voltage-free monostable relay contacts.

The module can activate output contacts one-by-one and is equipped with circuit checking for the unique control selection.


Field devices can be directly driven by on-board relays with gold-plated output contacts and an expected lifecycle of  $10^8$  operations. Each relay provides a 1500 Vrms coil contacts isolation.

Two outputs have SPDT (single-pole, double-throw: Common + NO + NC) contacts, while the other six are SPST (single-pole, single-throw: Common + NO).

The monostable command execution time is both hardware and software programmable. Using the latter, a short or long contact retention time can be specified by the incoming control message. The execution times are selectable in a range from 0.1 to 20 s with 0.1 s steps.

Several LEDs, located on the module's front edge, provide local fault indication and digital output status (one LED for each output), while an optional alphanumeric LCD display (mounted on the RTU cabinet) can monitor the module status, on request.

8 MOMENTARY DIGITAL OUTPUT MODULE – BLOCK DIAGRAM



SPECIFICATIONS

**Outputs**

8 timed contacts, retention time 0.1 to 20 s

**Maximum Power Requirements**

+5 V dc/5 mA, +12 V dc/20 mA (on relay activation)

**Isolation Voltage**

1500 Vrms (relay coil contacts), 1000 Vrms (contact-contact)

**Relay Specification**

Expected lifecycle: 10<sup>8</sup> operations, gold-plated contacts, voltage-free contacts

**Maximum Load (UL/CSA Rating)**

2 A at 30 V dc

**Maximum Switching Capacity (UL/CSA rating)**

dc ONLY  
60 W, 48 V

**Operating Temperature**

–25°C to +70°C

**Field Cable Connection**

Removable screw-terminal blocks on module's front edge

**Diagnostics and Status**

LED indicators on module's front edge



**The Foxboro Company**

33 Commercial Street  
Foxboro, Massachusetts 02035-2099

United States of America

<http://www.foxboro.com>

Inside U.S.: 1-508-543-8750 or 1-888-FOXBORO (1-888-369-2676)

Outside U.S.: Contact your local Foxboro representative.

Foxboro and I/A Series are registered trademarks of The Foxboro Company.

Invensys is a trademark of Invensys plc.

All other brand names may be trademarks of their respective companies.

Copyright 2001 The Foxboro Company

All rights reserved