


FoxRemote™ Configurations for Solaris® Remote Access for I/A Series® Application Workstations and Workstation Processors



OVERVIEW

The FoxRemote™ product is a bundled software solution that provides fast remote access to the I/A Series® process control system over a customer supplied network. With this type of remote access and depending upon the I/A Series system configuration, a remote session can display process graphics, use the System Monitor Display Handler to manage alarms, have limited use of configurators, and look at live and historical data.

BENEFITS

With the ability to connect to the process control system from virtually anywhere in the world, it is possible to provide quick response to process and business operation issues by enabling qualified personnel to access plant applications and information. A skilled plant engineer can thus provide valuable operation assistance from home or while on the road. Qualified personnel can offer assistance to other corporate locations without the associated lost travel time and expenses. These new levels of support quickly translate into faster response times, improved product quality, increased productivity and reduced operation costs.

PREREQUISITES

I/A Series System Requirements

- ▶ I/A Series Application Workstation 51 (AW51) or Workstation Processor (WP51) with optional IP Ethernet ports
- ▶ Additional I/A Series Display Managers or FoxView™ software licenses for each concurrent remote session
- ▶ I/A Series software Version 3.3 or better with functional IP network addressing

PC Requirements (Traditional X Clients)

- ▶ Must be running one of the following operating systems: Windows Vista®, Windows XP SP2, Windows XP x64 Edition, Windows® 2000 SP4, Windows Server® 2003, Windows Server 2003 x64 Edition, Windows Terminal Server Edition, Citrix® Presentation Server™ for Windows platforms and Windows XP Tablet PC Edition.
- ▶ At least 94 MB hard disk space for a typical installation.
- ▶ CD-ROM drive and a Windows compatible mouse.
- ▶ SVGA monitor and driver that supports a screen area of 1024 x 768 with a color setting of 256 or True Color.

PART NUMBER - Q0300HZ

The Traditional X Server (Q0300HZ) configuration allows access to the AW/WP for remote display managers and configurator access over the corporate network. This network can be as small as one PC directly connected to an AW/WP or as large as several PCs connected to several AW/WPs over the corporate network.

This is a TCP/IP connection so FTP Data for Windows and FoxExplorer software support is available.

Traditional X Server bundle. The Q0300HZ part number includes the following:

- ▶ One 5-user license pack of the standard X Server software that includes a CD-ROM and manuals.
- ▶ One *FoxRemote Installation and Configuration Guide* with a FoxRemote CD-ROM.

FoxRemote Abilities

- ▶ Allows Display Manager/FoxView Access
- ▶ Configurator Access
- ▶ VT100 Access
- ▶ File Transfers
- ▶ Data for Windows
- ▶ Alarm Acknowledgement

FoxRemote Limitation

Remote Audible Alarming