


I/A Series® Software

Foreign Device Real Output (FROUT) Block



The Foreign Device Real Output (FROUT) block provides the control strategy with output capability for a single real value in real-time to a PROFIBUS™-DP or Modbus™ remote I/O device via a Micro-I/A™ Station, or to a foreign device via an I/O gate. The block supports Auto/Manual control.

OVERVIEW

The Foreign Device Real Output (FROUT) block sends the real value received from the I/A Series control strategy to its applicable field device, only when it receives a changed value. The block can be configured to perform output once, change driven only, or during every execution regardless of input changes.

FROUT can provide values to:

- PROFIBUS-DP or Modbus remote I/O devices via a Micro-I/A Station

- foreign (third-party) devices⁽¹⁾ via an I/O gate.

The input value can be scaled if desired, and the output is modified accordingly.

As long as the block is in Auto and no error conditions exist, the value is moved from the block's connectable input parameter and sent to the Micro-I/A Station or I/O gate for delivery to the field device.

When the block is in Manual, processing of I/A Series data is suspended and the input is not sent to the field device by the block.

(1) Refer to *DDE I/O Gate* (PSS 21S-3A4 B3) for an explanation on how an I/O gate interfaces foreign devices.

Features

- Sends a single analog value to applicable field device
- Gain and bias terms for scaling input
- Manual/Auto control of the block output signal; can be initiated by a host process or another block
- Supports a series of validation checks to ensure process is on-line before block initialization
- Specification of source point for a PROFIBUS-DP or Modbus remote I/O device, or for a foreign device.

Principal Parameters**Input**

- 1 real input, derived from I/A Series control strategy
- Manual/Auto control mode switching
- Gain and Bias (real inputs for scaling).

Output

- 1 real output to applicable field device, in Auto mode.

SUPPORT

FROUT allows the following equipment to interface the applicable field devices:

- AW70 processors with control software (see *70 Series Application Workstation Model AW70* [PSS 21H-4U1 B3])
- AW51 processors (see *50 Series Application Workstation Model AW51* [PSS 21H-4R1 B3])
- Micro-I/A Station (see *Field Automation Subsystem Micro-I/A PROFIBUS-DP Remote I/O Interface* [PSS 21H-6C4 B4] or *Field Automation Subsystem Micro-I/A Modbus Remote I/O Interface* [PSS 21H-6C5 B4])
- I/O gate (see *DDE I/O Gate* [PSS 21S-3A4 B3]).

The Foxboro Company

33 Commercial Street
Foxboro, Massachusetts 02035-2099
United States of America
<http://www.foxboro.com>

Inside U.S.: 1-508-543-8750 or 1-888-FOXBORO (1-888-369-2676)
Outside U.S.: Contact your local Foxboro representative.

Foxboro, I/A Series, and Micro-I/A are trademarks of The Foxboro Company.
Invensys is a trademark of Invensys plc.
Modbus is a trademark of AEG Schneider Automation.
PROFIBUS is a trademark of the Profibus Users Organization (PNO).
All other brand names may be trademarks of their respective companies.

Copyright 2000 The Foxboro Company
All rights reserved