

FBM211, 0 to 20 mA Input Module



The FBM211, 0 to 20 mA Input Module contains sixteen 20 mA DC analog input channels.

OVERVIEW

The FBM211, 0 to 20 mA Input Module contains sixteen 20 mA DC analog input channels, each channel accepting a 2-wire analog sensor input such as a 4 to 20 mA transmitter or a self-powered 20 mA source. The input channels are galvanically isolated from ground and module logic. The module performs the signal conversion required to interface the electrical input signals from the field sensors to the redundant module Fieldbus.

FBM211 executes an analog input application program, which provides configurable options for Conversion Time and Rate of Change Limits.

FEATURES

Key features of the FBM211 are:

- ▶ Sixteen 20 mA DC analog input channels
- ▶ Each group of eight input channels is group isolated
- ▶ Rugged design suitable for enclosure in Class G3 (harsh) environments
- ▶ Execution of an analog input application program that provides conversion time and configurable options for Rate of Change Limits
- ▶ High accuracy achieved by sigma-delta data conversions for each channel

- ▶ Termination Assemblies (TAs) for locally or remotely connecting field wiring to the FBM211
- ▶ Termination Assemblies for external or FBM powered transmitters.

HIGH ACCURACY

For high accuracy, the module incorporates a multiplexed Sigma-Delta converter shared by all channels, which can provide new analog input readings every 100 ms, and a configurable integration period to remove any process noise and power line frequencies. Each time period, the FBM converts each analog input to a digital value, averages these values over the time period and provides the averaged value to the controller.

STANDARD DESIGN

FBM211 has a rugged extruded aluminum exterior for physical protection of the circuits. Enclosures specially designed for mounting the FBMs provide various levels of environmental protection, up to harsh environments, per ISA Standard S71.04.

VISUAL INDICATORS

Light-emitting diodes (LEDs) incorporated into the front of the module provide visual status indications of Fieldbus Module functions.

EASY REMOVAL/REPLACEMENT

The module can be removed/replaced without removing field device termination cabling, or power or communication cabling.

FIELDBUS COMMUNICATION

A Fieldbus Communications Module or a Control Processor interfaces to the redundant 2 Mbps module Fieldbus used by the FBMs. The FBM211 accepts communication from either path (A or B) of the 2 Mbps Fieldbus — should one path fail or be switched at the system level, the module continues communication over the active path.

MODULAR BASEPLATE MOUNTING

The module mounts on a 200 Series baseplate, which accommodates up to four or eight Fieldbus Modules. The Modular baseplate is either DIN rail mounted or rack mounted, and includes signal connectors for redundant Fieldbus, redundant independent DC power, and termination cables.

TERMINATION ASSEMBLIES

Field I/O signals connect to the FBM subsystem via DIN rail mounted TAs. The TAs used with the FBM211 are described in “TERMINATION ASSEMBLIES AND CABLES” on page 6.

FUNCTIONAL SPECIFICATIONS

Input

16 group isolated and independent channels

Input Range (each channel)

0 to 20.4 mA DC (each channel current limited to 33 mA)

Accuracy (includes linearity)

$\pm 0.03\%$ of span

Accuracy temperature coefficient: ± 50 ppm/ $^{\circ}$ C

Input Signal A/D Conversion

Each channel performs A/D signal conversion using a multiplexed Sigma-Delta converter.

Integration Period

Software configurable

Common Mode Rejection

>100 db at 50 or 60 Hz

Normal Mode Rejection

>35 db at 50 or 60 Hz

Input Channel Impedance

61.9 Ω nominal

Field Device Cabling Distance

Maximum distance of the field device from the FBM is a function of compliance voltage (23 V for internal power), wire gauge, and voltage drop at the field device.

Loop Power Supply Protection

Each channel is current limited and voltage regulated when used with TA RH916BT (supersedes P0916BT) or P0916BU that limits short circuit current to 35 mA. If the current limit circuit shorts out, the current is limited to about 385 mA.

HART® Protocol Compatibility

The channels meet the impedance requirements for a HART High Impedance Device and can be used in a HART loop without interfering with the HART signals between the field device and a Hand-Held Communicator (HHC).

If a FoxCom of HART transmitter is used with FBM211, a 200 ohm in-line resistor (assembly part number RH902VY (supersedes P0902VY)) must be added in series with the transmitter.

Input Channel Isolation

The channels are not galvanically isolated from each other, but are galvanically isolated from ground and module logic. Group isolated inputs use the FBM subsystem power supply for field power.

The module withstands, without damage, a potential of 600 V AC applied for one minute between the group isolated channels and earth (ground).

CAUTION

This does not imply that these channels are intended for permanent connection to voltages of these levels. Exceeding the limits for input voltages, as stated elsewhere in this specification, violates electrical safety codes and may expose users to electric shock.

Communication

Communicates with its associated FCM or FCP via the redundant 2 Mbps module Fieldbus

Power Requirements

INPUT VOLTAGE RANGE (REDUNDANT)

24 V DC +5%, -10%

CONSUMPTION

7 W (maximum) at 24 V DC

11 W (maximum) at 24 V DC with all inputs at 20.4 mA (internal power)

HEAT DISSIPATION

3 W (maximum) at 24 V DC

Calibration Requirements

Calibration of the module and termination assembly is not required.

FUNCTIONAL SPECIFICATIONS (CONTINUED)

Regulatory Compliance

ELECTROMAGNETIC COMPATIBILITY (EMC)

European EMC Directive 2004/108/EC (Prior to April 20, 2016) and 2014/30/EU (Beginning April 20, 2016)

Meets: EN61326-1:2013 Class A Emissions and Industrial Immunity Levels

RoHS COMPLIANCE

Complies with European RoHS Directive 2011/65/EU

PRODUCT SAFETY

Underwriters Laboratories (UL) for U.S. and Canada

UL/UL-C listed as suitable for use in UL/UL-C listed Class I, Groups A-D; Division 2; temperature code T4 enclosure based systems when connected to specified Foxboro Evo processor modules as described in the *Standard and Compact 200 Series Subsystem User's Guide* (B0400FA). Communications circuits also meet the requirements for Class 2 as defined in Article 725 of the National Electrical Code (NFPA No.70) and Section 16 of the Canadian Electrical Code (CSA C22.1). Conditions for use are as specified in the *Standard and Compact 200 Series Subsystem User's Guide* (B0400FA).

European Low Voltage Directive 2006/95/EC (Prior to April 20, 2016) and 2014/35/EU (Beginning April 20, 2016) and Explosive Atmospheres (ATEX) directive 94/9/EC (Prior to April 20, 2016) and 2014/34/EU (Beginning April 20, 2016)

DEMKO certified as Ex nA IIC T4 for use in certified Zone 2 enclosure when connected to specified I/A Series processor modules as described in the *Standard and Compact 200 Series Subsystem User's Guide* (B0400FA). Also see, Table 1 on page 7.

MARINE CERTIFICATION

ABS Type Approved and Bureau Veritas Marine certified for Environmental Category EC31.

ENVIRONMENTAL SPECIFICATIONS⁽¹⁾

Operating

TEMPERATURE

Module

-20 to +70° C (-4 to +158° F)

RELATIVE HUMIDITY

5 to 95% (noncondensing)

ALTITUDE

-300 to +3,000 m (-1,000 to +10,000 ft)

Storage

TEMPERATURE

-40 to +70° C (-40 to +158° F)

RELATIVE HUMIDITY

5 to 95% (noncondensing)

ALTITUDE

-300 to +12,000 m (-1,000 to +40,000 ft)

Contamination

Suitable for use in Class G3 (Harsh) environments as defined in ISA Standard S71.04, based on exposure testing according to EIA Standard 364-65, Class III.

Vibration

0.75 m/S² (5 to 500 Hz)

PHYSICAL SPECIFICATIONS

Mounting

MODULE

FBM211 mounts on a Modular baseplate. The Modular baseplate can be mounted on a DIN rail (horizontally or vertically), or horizontally on a 19-inch rack using a mounting kit. Refer to PSS 31H-2SBASPLT for details.

TERMINATION ASSEMBLY

The TA mounts on a DIN rail and accommodates multiple DIN rail styles including 32 mm (1.26 in) and 35 mm (1.38 in).

Weight

MODULE

284 g (10 oz) approximate

TERMINATION ASSEMBLIES

Compression

272 g (0.60 lb, approximate)

Dimensions - Module

HEIGHT

102 mm (4 in), 114 mm (4.5 in) including mounting lugs

WIDTH

45 mm (1.75 in)

DEPTH

104 mm (4.11 in)

Dimensions - Termination Assemblies

Refer to page 9.

Part Numbers

FBM211 MODULE

RH914TN (supersedes P0914TN)

TERMINATION ASSEMBLIES

See "FUNCTIONAL SPECIFICATIONS - TERMINATION ASSEMBLIES" on page 7.

Termination Cables

CABLE LENGTHS

Up to 30 m (98 ft)

CABLE MATERIALS

Polyurethane or Low Smoke Zero Halogen (LSZH)

TERMINATION CABLE TYPE

Type 4 - Refer to Table 2.

CABLE CONNECTION

37-pin male D-subminiature

(1) The environmental limits of this module may be enhanced by the type of enclosure containing the module. [Refer to the applicable Product Specification Sheet (PSS) which describes the specific type of enclosure that is to be used.]

PHYSICAL SPECIFICATIONS (CONTINUED)

Construction - Termination Assembly

MATERIAL

Polyamide (PA), compression

TERMINAL BLOCKS

Inputs - 2 tiers, 16 positions

Field Termination Connections

COMPRESSION - ACCEPTED WIRING SIZES

Solid/Stranded/AWG

0.2 to 4 mm²/0.2 to 2.5 mm²/24 to 12

AWG

Stranded with Ferrules

0.2 to 2.5 mm² with or without plastic collar

TERMINATION ASSEMBLIES AND CABLES

Field I/O signals connect to the FBM subsystem via DIN rail mounted termination assemblies, which are electrically passive. TAs for the FBM211 module are available in the following forms:

- ▶ Compression screw type using Polyamide (PA) material

Each FBM211 Termination Assembly and its associated termination cable provide feedthrough connection between sixteen 2-wire analog input signals and the FBM211.

Loop power is provided to the field devices by a customer-supplied external DC power supply or by the FBM auxiliary +24 V DC power supply depending on the TA selected.

A removable termination cable connects the DIN rail mounted TA to the FBM via a field connector on the baseplate in which the FBM is installed. Termination cables are available in the following materials:

- ▶ Polyurethane
- ▶ Low Smoke Zero Halogen (LSZH).

Termination cables are available in a variety of lengths, up to 30 meters (98 feet), allowing the termination assembly to be mounted in either the enclosure or in an adjacent enclosure. See Table 2 for a list of termination cables used with the TAs for the FBM211.

FUNCTIONAL SPECIFICATIONS - TERMINATION ASSEMBLIES

FBM Type	Input Signal	TA Part Number (a)	TA Part Number (b)	Termination Type (c)	TA Cable Type (d)	TA Certification Type (e)
		PA	PVC			
FBM211	Loop power is provided to the field devices by a customer-supplied external DC power supply.	RH916JT (supersedes P0916JT)	P0916PQ ^(f)	C RL	4	1,2
FBM211	Loop power is provided to the field devices by the FBM auxiliary +24 V DC power supply.	RH916BT (supersedes P0916BT)	P0916BU ^(f)	C RL	4	1,4

- (a) PA is polyamide rated from -20 to +70°C (-4 to +158°F)
 (b) PVC is polyvinyl chloride rated from -20 to +50°C (-4 to +122°F.)
 (c) C = TA with compression terminals.
 (d) See Table 2 for cable part numbers.
 (e) See Table 1 for Termination Assembly certification definitions.
 (f) This is not a RoHS part.

Table 1. Certification for Termination Assemblies

Type	Certification
Type 1	TAs are UL/UL-C listed as suitable for use in Class I; Groups A-D; Division 2 temperature code T4 hazardous locations. They are DEMKO certified EEx nA IIC T4 for use in Zone 2 potentially explosive atmospheres.
Type 2	TAs are UL/UL-C listed as associated apparatus for supplying non-incendive field circuits Class I; Groups A-D; Division 2 hazardous locations when connected to specified 200 Series FBMs and field circuits meeting entity parameter constraints specified in <i>Standard and Compact 200 Series Subsystem User's Guide</i> (B0400FA). They are also DEMKO certified as associated apparatus for supplying field circuits for Group IIC, Zone 2 potentially explosive atmospheres. Field circuits are also Class 2 limited energy (60 V DC, 30 V AC, 100 VA or less) if customer-supplied equipment meets Class 2 limits.
Type 4	All field circuits are Class 2 limited energy (60 V DC, 30 V AC, 100 VA or less) if customer-supplied equipment meets Class 2 limits.

Table 2. Cables Types and Part Numbers

Cable Length m (ft)	Type 4 P/PVC^(a)	Type 4 LSZH^(b)
0.5 (1.6)	RH916FG (supersedes P0916FG)	RH928BA (supersedes P0928BA)
1.0 (3.2)	RH916FH (supersedes P0916FH)	RH928BB (supersedes P0928BB)
2.0 (6.6)	RH931RQ (supersedes P0931RQ)	RH928BC (supersedes P0928BC)
3.0 (9.8)	RH916FJ (supersedes P0916FJ)	RH928BD (supersedes P0928BD)
5.0 (16.4)	RH916FK (supersedes P0916FK)	RH928BE (supersedes P0928BE)
10.0 (32.8)	RH916FL (supersedes P0916FL)	RH928BF (supersedes P0928BF)
15.0 (49.2)	RH916FM (supersedes P0916FM)	RH928BG (supersedes P0928BG)
20.0 (65.6)	RH916FN (supersedes P0916FN)	RH928BH (supersedes P0928BH)
25.0 (82.0)	RH916FP (supersedes P0916FP)	RH928BJ (supersedes P0928BJ)
30.0 (98.4)	RH916FQ (supersedes P0916FQ)	RH928BK (supersedes P0928BK)

(a) P/PVC is polyurethane outer jacket and semi-rigid PVC primary conductor insulation. PVC is rated from -20 to +50°C (-4 to 122°F).



(b) Low smoke zero halogen or low smoke free of halogen (LSZH) is a material classification used for cable jacketing. LSZH is composed of thermoplastic or thermoset compounds that emit limited smoke and no halogen when exposed to high sources of heat. Temperature range; -40 to +105°C (-40 to +221°F)

DIMENSIONS – NOMINAL



[mm]
in

Compression Termination Assembly

RH916JT (supersedes P0916JT), RH916BT (supersedes P0916BT),



Ring Lug Termination Assembly



(a) Overall width – for determining DIN rail loading.

(b) Height above DIN rail (add to DIN rail height for total).

RELATED PRODUCT SPECIFICATION SHEETS (PSS)

PSS Number	Description
PSS 31H-2SOV	Standard 200 Series Subsystem Overview
PSS 31H-2CERTS	Standard and Compact 200 Series I/O, Agency Certifications
PSS 31H-2SBASPLT	Standard 200 Series Baseplates
PSS 21S-3CP270IC	Control Processor 270 (CP270) Integrated Control Software
PSS 31S-3FCPICS	Field Control Processor 280 (CP280) Integrated Control Software

Foxboro
by Schneider Electric

Invensys Systems, Inc.
38 Neponset Avenue
Foxborough, MA 02035-2037
United States of America
www.schneider-electric.com

Global Customer Support
Inside U.S.: 1-866-746-6477
Outside U.S.: 1-508-549-2424
Website: <https://support.ips.invensys.com>

Copyright 2015-2016 Invensys Systems, Inc.
All rights reserved.
Invensys is now part of Schneider Electric.

Schneider Electric, Invensys, Foxboro, Foxboro Evo, FoxCom, and I/A Series, are trademarks owned by Schneider Electric SE, its subsidiaries and affiliates. All other trademarks are the property of their respective owners.

MB 031

0816