



Foxboro™ DCS

Positional/Rate Limiter (LIM) Block

PSS 41S-3LIM

Product Specification

May 2019



Legal Information

The Schneider Electric brand and any trademarks of Schneider Electric SE and its subsidiaries referred to in this guide are the property of Schneider Electric SE or its subsidiaries. All other brands may be trademarks of their respective owners.

This guide and its content are protected under applicable copyright laws and furnished for informational use only. No part of this guide may be reproduced or transmitted in any form or by any means (electronic, mechanical, photocopying, recording, or otherwise), for any purpose, without the prior written permission of Schneider Electric.

Schneider Electric does not grant any right or license for commercial use of the guide or its content, except for a non-exclusive and personal license to consult it on an "as is" basis. Schneider Electric products and equipment should be installed, operated, serviced, and maintained only by qualified personnel.

As standards, specifications, and designs change from time to time, information contained in this guide may be subject to change without notice.

To the extent permitted by applicable law, no responsibility or liability is assumed by Schneider Electric and its subsidiaries for any errors or omissions in the informational content of this material or consequences arising out of or resulting from the use of the information contained herein.


Overview

The positional/rate Limiter (LIM) block is a signal positional/rate limiter for high-low absolute and rate-of-change limiting of the measurement input.

The LIM block provides rate-of-change limiting and high-low absolute limiting of the measurement input at the block's output. Rate-of-change limiting is performed on an optional basis. The amount of rate limiting is determined by the rate-of-change limit parameter, which represents the maximum absolute rate-of-change that the output can exhibit. A scaling factor specifies the units of time of the rate-of-change parameter so that the ratio of the fixed units of the measurement signal are dimensionally compatible with the rate-of-change over the block's time interval. Also provided are user-specifiable high and low engineering unit scales for the output and variable output limits. The block supports auto/manual output control. An input forces the output to track the measurement.

Standard Features

- Manual/Auto control of output
- Follow input
- High-low absolute limiting (clamping) with Boolean output indicators
- Option: Rate-of-change limiting with Boolean output indicator

 **WARNING:** This product can expose you to chemicals including lead and lead compounds, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information, go to www.p65warnings.ca.gov/.

Schneider Electric Systems USA, Inc.
38 Neponset Avenue
Foxborough, Massachusetts 02035–2037
United States of America

Global Customer Support: <https://pasupport.schneider-electric.com>

As standards, specifications, and design change from time to time, please ask for confirmation of the information given in this publication.

© 2014–2019 Schneider Electric. All rights reserved.

PSS 41S-3LIM, Rev A