


Foxboro Evo™ SCD6000 8 Channel Serial Module



OVERVIEW

The 8 Channel Serial Module provides multiple configurable communications ports with protocol support for DNP3 Master and Slave, Modbus Master, and Slave, and IEC101 Master. Proprietary protocols may be configured by the user using the configurable State and Logic Language High Level Serial Interface functions (refer Foxboro Evo™ SCD6000 SALL PSS 31S-2M15).

The first four channels (1-4) provide isolated RS-485 half-duplex (2-wire) interfaces, ideal for long cable runs, large networks, and noisy environments. Duplicated signal connections on the 2-wire RS-485 interface allow simple wiring of multi-drop configurations. Channels are slew-rate limited to

minimize interference to other systems and to reduce the effect of cabling and terminations. Surge ground and current limited screen connections are provided on isolated 2-wire ports to assist noise and electrostatic discharge immunity.

The other four channels (5-8) are independently configurable for RS-232, RS-485 full duplex (4-wire), or RS-485 half-duplex (2-wire) connection. RS-485 4-wire operation is compatible with RS-422 devices. The differential signalling of the RS-485 and RS-422 standards provide high tolerance to noise and differences in ground potential.

RS-232 hardware flow control is provided on Channels 5-8. RS-232 level modem control is available on Channels 5-8 for RS-232 and RS-485 configurations for use in SALL HLSI allows hardware flow and/or modem control in user develop protocols.

INTRODUCTION

The 8 Channel Serial Module provides a flexible and cost effective method for communicating with a multitude of intelligent field devices or master devices. The module facilitates point-to-point and multi-drop communication with a wide range of electronic flow meters, analytical devices, relays, circuit breakers and other intelligent devices. Each of the eight ports may be configured to support communication to master or slave devices via the DNP3 Master and Slave, Modbus Master and Slave, IEC101 Master, or user configurable protocols. When combined with the main processor's programming capabilities, the 8 Channel Serial Module provides a powerful interface for gathering data from OEM devices.

FEATURES

- ▶ Eight channels per module
 - Four isolated RS-485 2-wire ports
 - Four RS-232 or RS-485 (2-wire or 4-wire) ports
- ▶ LED indication of communications activity on each channel
- ▶ Data rate: 50 to 38400 bps
- ▶ Hardware handshake on RS-232
- ▶ RS-232 modem control available on RS-232/RS-485 selectable ports
- ▶ Supports the following protocols
 - DNP3 Master
 - DNP3 Slave
 - Modbus Master
 - Modbus Slave
 - IEC101 Master
 - User configured via SALL HLSI functions
- ▶ Supports the following functionalities
 - Terminal Server
 - Diag Router
 - Diag Server
 - Analogger
 - Event Logger
- ▶ Slew-rate limited
- ▶ High electrostatic discharge immunity on all ports
- ▶ High isolation transceiver on 2-wire ports
- ▶ Surge ground and screen connection on 2-wire ports.

FUNCTIONAL SPECIFICATIONS

General

16550 type two quad UART devices with a 64 character FIFO on each transmitter and receiver

Indications

Transmit LED and Receive LED (yellow) for each channel, Run/Fail LED (green/red) for the module

Data Rate

50 to 38400 baud (dependent on protocol configuration options)
RS-232 and RS-485 ports are slew-rate limited

Communications Protocols

DNP3 Master, DNP3 Slave
Modbus Master, Modbus Slave
SALL HLSI

Channels 1 Through 4

INTERFACE

RS-485 2-wire (Compatible with CCITT.V.11 and TIA/EIA-485-A)
8 way plug-in screw type terminals (Phoenix MC 1.5-3,81 series)

ISOLATION

1kV rms (1 minute)
Galvanic isolation (data lines from the logic circuits)
Surge ground and screen connection

DRIVER CAPABILITY

1000 pF or 1200 m, 32 unit drive, 1 unit loading

Channels 5 Through 8

INTERFACE

Link configurable as RS-232, RS-485 2-wire or RS-485 4-wire, DB9 Male, modified TIA/EIA-574 (PC-compatible RS-232)
RS-232 hardware flow control
RS-232 level modem control for RS-232 and RS-485 configurations

ISOLATION

Direct connection (± 7 V common mode on RS-422/RS-485)
High electrical discharge immunity

DRIVER CAPABILITY

RS-232: 1000 pF or 15 m, ± 5 V drive
RS-485: 1000 pF or 120 m, 32 unit drive, $\frac{1}{4}$ unit loading

NOTE

RS-485 4-wire is RS-422 level compatible.

PIN ASSIGNMENT

Table 1. Channels 1 through 4

Pin	RS-485 (2-wire) Isolated
1	Transmit/Receive Data B (+)
2	Transmit/Receive Data A (-)
3	Signal Ground
4	Chassis - connected to SCD frame
5	Chassis - connected to SCD Frame
6	Single Ground
7	Transmit/Receive Data A (-)
8	Transmit/Receive Data B (+)

Table 2. Channels 5 through 8

Pin	Direction	RS-232	RS-485 (4-wire)	RS-485 (2-wire)
1	In	Signal Detect*	–	–
2	In	Receive Data	Receive Data B (R+)	–
3	Out	Transmit Data	Transmit Data A (T–)	Transmit/Receive A (–)
4	Out	Data Terminal Ready*	–	–
5	–	Signal Common	Signal Common	Signal Common
6	In	Data Set Ready*	–	–
7	Out	Request To Send*	Transmit Data B (T+)	Transmit/Receive B (+)
8	In	Clear To Send*	Receive Data A (R–)	–
9	In	Ring Indicator*	–	–

NOTES

1. Minimum RS-232 connections Receive Data, Transmit Data, and Signal Common Signals, marked with asterisks (*), do not require connection.
2. Null modem connections may be used.
3. Where collision detection is not provided, the state of Signal Detect is ignored.
4. Data Terminal Ready is asserted after the port is configured.
5. Request To Send is asserted during the transmission of data.

ENVIRONMENTAL SPECIFICATIONS**Operating Temperature****STANDARD**

0°C to 60°C (32°F to 140°F)

Humidity

10 to 95% (noncondensing)

PRODUCT SAFETY

This product complies with the U.S. Standard for Safety UL 61010-1 - Safety requirements for Electrical equipment for measurement, control, and laboratory use - PART 1: GENERAL REQUIREMENTS - Edition 2 - Revision Date 2008/10/28 and CSA C22.2 NO. 61010-1 - Safety requirements for Electrical equipment for measurement, control, and laboratory use.

PHYSICAL SPECIFICATIONS

Physical Size

187 mm x 262 mm x 35 mm

ORDERING INFORMATION

Part Number	Description
SY-0399132	8 Channel Serial Module



Invensys Systems, Inc
10900 Equity Drive
Houston, TX 77041
United States of America
<http://www.invensys.com>

Global Customer Support
Inside U.S.: 1-866-746-6477
Outside U.S.: 1-508-549-2424
Website: <https://support.ips.invensys.com>

Copyright 2015 Invensys Systems, Inc.
All rights reserved.
Invensys is now part of Schneider Electric.

Schneider Electric, Invensys, Foxboro, Foxboro Evo, FoxCom, and I/A Series, are trademarks owned by Schneider Electric SE, its subsidiaries and affiliates. All other trademarks are the property of their respective owners.

MB 031

0315