


**InBatch™ V9.5 With SP1 Software**



*InBatch™ software enables comprehensive batch control solutions to process industries, such as food, beverage, pharmaceuticals, and fine chemicals.*

InBatch software is a flexible batch management system that automates batch processes and provides a complete production history. Consistent with the Instrumentation, Systems, and Automation Society of America ANSI/ISA 88.01 - 1995 standard, InBatch software allows you to quickly and easily create recipes and simulate their execution against a model of the process - all before writing one line of control code. InBatch software also provides a complete material genealogy.

InBatch software features include:

- ▶ Field-proven batch engine
- ▶ Redundant Batch Server option
- ▶ Material genealogy
- ▶ Integrated Batch human interface (Batch View) when installed to work with I/A Series® software
- ▶ Integration with FoxView™ software, FoxAlert™ software, Sequential Function Chart and Structured Text (SFC/ST) Display Manager, and AIM\*AT® software when installed to work with I/A Series software
- ▶ Integration with Archestra® System Platform, Galaxy Repository, Wonderware® InTouch® software and Wonderware Historian software when installed to work with the Foxboro Control Software (FCS)
- ▶ Batch History data access via Wonderware Information Server (WIS)

- ▶ Web-based reporting leveraging Microsoft® Reporting Services
- ▶ FoxBatch™, I/A Series Batch, and InBatch Application Migration
- ▶ With the purchase of Wonderware Enterprise Integrator and additional services, comprehensive Enterprise Application Integration (EAI) solutions can be implemented for InBatch software using World Batch Forum Business to Manufacturing (B2MML) schema, based on the ISA-95 standard.
- ▶ Aid to customer compliance with FDA 21 CFR Part 11 on Electronic Records and Electronic Signatures.

InBatch software offers these significant benefits:

- ▶ Reduces the life-cycle engineering effort and facilitates recipe development and updating
- ▶ Reduces dependence on system experts (recipe configuration can be done by process engineers or chemists)
- ▶ Speeds batch processing for greater production capability
- ▶ Produces more consistent batches that meet tighter tolerances
- ▶ Provides flexibility for manufacturing different products, grades of products, and quick switchover between products
- ▶ Offers extensive data collection and batch production reports that help in production tuning and in meeting FDA requirements
- ▶ Provides expandability from entry level system to large installations while maintaining full functionality.

## OVERVIEW

InBatch software is an easy-to-use graphical control package that requires no programming. A model of the process is created interactively on workstation

display screens with icons and selections from pull-down menus. Recipes are configured by specifying unit and phase data interactively. The recipes are represented graphically in IEC 61131-3 based sequential function charts.

InBatch software provides recipe management, production information management functions, and an appropriate environment for hierarchical structuring of batch process control.

InBatch software has a hierarchical management and control structure that allows plant engineers to maintain the system easily. By splitting the logic into real-time process control (the phases running in sequence blocks) and supervisory (Batch) control, a top-down/bottom-up approach allows a structured and efficient implementation of batch projects. All configuration data, recipes, and batch records are kept in relational databases.

Integration of the Batch system with enterprise and Manufacturing Execution Systems (MES) modules enables a more complete batch management solution including equipment and production performance and optimization.

## INSTALLATION OPTIONS

InBatch v9.5 with SP1 software can be installed with or without I/A Series software components that enable tighter integration to the I/A Series distributed control system. The I/A Series software components include the I/A Series driver communication software via FoxAPI, I/A Series Tag Linker, as well as the I/A Series extensions to the runtime batch scheduling and display interfaces and batch reporting.

Installing InBatch software without the I/A Series components enables a tighter integration to the ArchestrA system platform, security, Galaxy Repository, and use of the I/A Series Device Integration Object (IADI) and/or the I/A Series Data Access Server (IADAS) for communication to the I/A Series DCS as typically delivered in a Foxboro

Control Software solution.




Figure 1. InBatch Installation Dialog Box

## PROCESS MODELING

A batch processing plant is made up of units, process classes, connections, transfer classes, process phases, and transfer phases.

- ▶ A unit is a group of equipment that processes materials such as reactors, mixers, blenders, trains and retorts. A unit can also simply hold materials. Examples of units are reactors, holding tanks, bulk storage vessels, filling stations, and manual addition stations.
- ▶ Process classes are groups of units. Each unit in the class has the same processing capabilities and/or performs the same function.
- ▶ Connections define a group of equipment that transfers material from a source unit to a destination unit.
- ▶ Transfer classes define a group of connections where all source units are in the same process class and all destination units are in the same process class.
- ▶ Process phases with their parameters define the capability of process classes.
- ▶ Transfer phases with their parameters define the capabilities of transfer classes.

InBatch software supports three approaches to structuring the batch process plant into the process model:

- ▶ Comprehensive model
- ▶ Connectionless model
- ▶ Hybrid model.

The comprehensive model uses all the available configuration tools of the InBatch software including process classes as well as transfer classes, while the connectionless model deals only with the definition of process classes. In this case, the movement of material between units is accomplished using complementary transfer phases that are assigned to a process class rather than to a transfer class. The hybrid model uses a combination of the comprehensive and connectionless models, maximizing the benefits of both approaches. To decide which approach is optimal for your specific application, analyze the batch philosophy of your company, the process being modeled, the flexibility requirements, the user interface requirements, and the historical batch recording requirements.

An integral part of process modeling involves defining specific data points, called tags, for units, processes, connections, and transfers. Tags allow the mapping of data between InBatch software and the controllers.

The process model also specifies the relationship between the tags used in workstations and controllers. Initially, InBatch software generates default relationships which can be modified during the modeling process.

The process model allows each process variable to have a unit of measure assignment. This unit of measure attribute is assigned to the formula parameter, such as Degrees Fahrenheit for the formula parameter named Temperature. The Process

Model Editor also provides an enumeration data class option. This option allows the assignment of a Set Name to a list of integer values, each one having a corresponding alphanumeric string value. An example might be Automatic -2, Semi-Auto -1, and Manual -0.

### **Run-Time Model Edits**

The physical model of the plant can be edited while the system is running. Edits are actually made to a different database than that used by the run-time system. To effect the model changes, the InBatch run-time applications must be stopped, an “update run-time” action must be taken, and then the InBatch run-time applications can be started. These actions are performed from the Environment display.

### **Automatic Tag Creation**

The capability to automatically add, change, delete, and assign all phase parameter, control and status tags is provided, significantly reducing the time it takes to build a physical model of a plant.

## **MATERIALS TRACKING**

Materials tracking defines materials as ingredients, intermediates, finished goods, by-products and others, and includes the characteristics of each material. The batch materials database is used to automatically track the location of materials stored in different units.

The batch management function uses the ingredients' location data to get ingredients during the manufacture of a batch. This capability allows ingredient locations to be independent of recipes and control programs and permits ingredients to change location with no effect on recipe execution provided that a comprehensive process model is used.

The unit location can be entered in the materials database by plant personnel when new ingredients are received. A lot identification can also be assigned

to a material, and multiple lots of the same ingredient can be stored in the same vessel.

The batch management system updates the database when ingredients are used and when intermediates and finished goods are produced. The materials database provides easy access to work-in-process (WIP) information and can be used to update higher level management and Material Resource Planning (MRP) systems with ingredient usage, work-in-process, and finished goods production information. Materials tracking can be used to complement an existing inventory system.

## **PROCESS MANAGEMENT**

### **Batch Scheduling**

A batch is scheduled by entering the campaign, lot, batch, and recipe name. The train also needs to be selected with the batch size and the mode. The mode can be automatic, semi-automatic, or manual.

**AUTO:** In automatic mode, the default mode, the unit operations and phases are activated automatically as specified in the recipe. If the option is enabled, the operator can abort any phase and the batch auto-switches to the semi-automatic mode.

**SEMI-AUTO:** In semi-automatic mode, the operator must start each phase manually. The order of phases is specified in the recipe.

**MANUAL:** In manual mode, the operator can select any available phase in the recipe to be performed next. For example, manual mode allows an operator to retry a failed phase or to choose DISCHARGE and dump a batch immediately.

The batch scheduling function maintains a list of batches to be produced and allows priority based execution of batches, where the priorities can be manually specified or modified.

## Batch Validation

A batch must be validated before it can execute.

Validation of a batch consists of:

- ▶ Verification of recipe existence in the database
- ▶ Verification of process model references made from the recipe
- ▶ Verification of materials database references made from the recipe
- ▶ Verification of train existence
- ▶ Verification of the batch size against the allowed boundaries.

## Batch Management

The Batch Manager directs and supervises the execution of the batches. Based on the recipe procedure, phases are executed in sequential and parallel fashions after checking that the appropriate transition conditions are satisfied.

The Batch Manager also interfaces with batch display modules and provides operators with information on the batches running in the system. The Batch Manager coordinates the usage of process units for each batch and allocates units as they are available, within the specified train. Unit selection can also be done manually. The Batch Manager captures all batch execution events and operator activities during the execution of a batch and sends this information to the Batch History database.

## Restart Capability

Batch Manager has the capability to restore the previously known-good state of the system upon restart after unexpected system shutdowns. As the batch management system executes batches, all batch execution and equipment allocation information is written to multiple data files. If a system failure occurs, these files are read by the batch

management system when restarted. The data in these files allows the batch management system to resume batch operation.

To maintain the exact state of the batch in these data files when power fails, an uninterruptable power supply (UPS) is required on the Batch server. The UPS allows for an orderly shutdown of the Batch server to preserve batch state data.

## Simulating Batches

InBatch software allows batches to be run in a simulation mode, where batches are created and run without actually starting the phases in a control processor. You specify a global phase duration time to permit operator interaction during the simulated execution.

## Recipe Procedure Jumps

The Batch View allows you, as the operator, to jump forward or backward in the recipe procedure and edit phase parameters (formula). To enter the jump mode, the batch must be in the Held state.

After exiting the jump mode, you can restart the batch at the selected procedure. All events are logged by the Batch Historian.

## Save Control Recipe as Master Recipe

At batch completion, as an operator, you may save 1) all phase parameter edits, and/or 2) the equipment used (creating an equipment-dependent recipe), as a master recipe. You have the option to overwrite the existing master recipe increasing the version level, or to save it as a new master recipe. You are required to enter a user name and, if desired, may enter a comment. You must have an appropriate security role for a save to occur.

### **Viewing Transition Logic Status**

Transition logic expressions, their description and status can be viewed at run time. Additionally, the ability to force a transition to a true state is provided.

### **View and Edit Phase Parameter Values**

Phase configuration and phase parameters can be edited for any batch that has a Ready, Run, Done, Held or Aborted status. All edits are saved to history. This includes changed formula parameters, phase instructions and enabling or disabling comment required or operator acknowledgment (Ack on Entry or Exit).

### **Operator Entered Comments**

A comment may be entered and saved to history for any batch that has a Ready, Run, Done, Held or Aborted status.

### **Display Equipment Name on Procedural Element**

The actual unit or connection name that is allocated is displayed on the unit operation procedural element.

### **Print Schedule**

Use this feature to print the list of scheduled batches.

### **View Schedule**

In order to manage large numbers of scheduled batches, you may specify view and filter criteria by which the Batch Scheduler application alters the list of scheduled batches.

The function supports user selection of trains, recipes, recipe types, recipe states, or specific campaign, lot, and/or batch information (refer to Figure 2). The scheduler then presents a list of batches that match the criteria.

### **View and Edit Equipment Allocation Queue**

From the Batch Scheduler and Batch Display, you can review equipment allocation, release equipment, and switch allocation to a different piece of equipment.

If you need to ensure that the equipment will be ready before batch processing begins, you can manually allocate equipment for a batch.

### **Automatic Creation of Batch ID using User Prefix**

The capability to append a numerical character to a user-defined Batch ID prefix has been provided.




Figure 2. Batch Schedule Display (InBatch with I/A Series Components Version)

## RECIPE MANAGEMENT

The recipe management function provides the environment to configure, copy, and modify master recipes in an IEC 61131-3 graphical environment. The recipe structures follow the ANSI/ISA 88.01 - 1995 standard and support all three levels of the standard: unit procedure, unit operation, and phase. Refer to Figure 3.

An option allows the recipe to collapse to two levels: unit procedure and phases. To migrate three-level recipes to two levels, unit operations become unit procedures.

InBatch software provides the environment for maintaining version history of a master recipe with date and time stamp, author name, and optional comments. Up to five levels of recipe approvals can be implemented.

A master recipe is scalable to the batch size specified manually or by production schedule. All formula quantities for ingredients, intermediates, by-

products, and finished goods are scalable and can be entered either as actual quantities or as a percent of the total batch size.

## Recipe Database Import and Export

The Recipe Editor features an import and export capability that allows you to move recipes from one recipe database to another. The export function creates a binary file of one or more selected recipes to the local hard drive.

## Approved for Test

A recipe can be "Approved for Test". Any recipe that is "Approved for Test" may be scheduled.

## Formula Association to Procedure

The ability to associate formula input, output, and process variable values to phases and to easily edit them from the formula display is provided.






Figure 3. Batch Recipe Structure

**Recipe Unit Procedure and Operation Libraries**

You can save unit procedures to a procedures library and unit operations to an operations library. To accomplish this, you drag and drop the procedure or operation object on the appropriate library display. You can also retrieve and insert a procedure or operation from the appropriate library into a recipe procedure or operation in the same manner.

**Recipe Types**

You have the ability to define recipe types. This allows you to group recipes for easy retrieval and scheduling. Examples of recipe types include clean-in-process, barbecue sauce, salad dressing.

**Recipe States**

You have the ability to define recipe states. Examples of these states include Development, Production, Test, Review, Archive, and so forth. This allows you



to group recipes for easy retrieval for editing.

### **Recipe Selection, Filtering, and Sorting**

In order to manage large numbers of recipes, you can set the filter by state or type and can sort the list of recipes by Recipe ID, Recipe Name, State or Type.

### **Propagation of Process Model Changes**

The Recipe Editor provides a function to automatically propagate phase changes in the process model to all the affected recipes.

### **Recipe Editing Tools**

Cut, copy, and paste menu commands and tools provide flexibility when editing elements in the recipe procedure.

### **Recipe Validation**

The validation function allows you to validate one or all recipes to verify that:

- ▶ The process model database information used in the recipe exists
- ▶ The material database information used in the recipe exists
- ▶ The minimum, maximum, and default batch sizes defined in the recipe header are appropriate
- ▶ All the formula parameters defined in the recipe procedure are linked to the appropriate information
- ▶ All reports triggered by phases exist in the reporting database
- ▶ All transition logic, including loop logic, is valid.

### **Recipe Configuration Reports**

You can print recipe configuration reports using the available report templates. The print preview option allows you to view the report before sending it to the printer, which can be a non-PostScript™ printer (refer to Figure 4).

Recipe Editor - RED\_004

Print... Next Page Prev Page Two Page Zoom In Zoom Out Close

RECIPE ID - RED\_004 VERSION #11 - 7/21/2009 9:23:05 AM

RECIPE PROCEDURE

Label	Instance	Unit Procedure	Operation	Phase
2	REACT TO ST	PREP MIXER	PREP MIXER	Alloc Transfer
3	REACTORS	PREP MIXER	PREP MIXER	N2 PURGE
4	REACTORS	PREP MIXER	PREP MIXER	TEMP CONTROL
5	REACTORS	PREP MIXER	PREP MIXER	BASE_ADD
7	Transition Name: 7		DESC:	
8	Transition Name: 8		DESC:	
6	REACTORS	PREP MIXER	PREP MIXER	AGITATE
10	ING TO REACT	ADD COLOR	ADD COLOR	INGRED_ADD
1	Transition Name: 1		DESC:	
11	REACTORS	FINISH BATCH	FINISH BATCH	GLOSS FEED
12	REACTORS	FINISH BATCH	FINISH BATCH	TEMP_CONTROL
13	Transition Name: 13		DESC:	
14	REACTORS	FINISH BATCH	FINISH BATCH	AGITATE
15	REACTORS	FINISH BATCH	FINISH BATCH	TEMP CONTROL
16	REACT TO ST	FINISH BATCH	FINISH BATCH	DISCHARGE
17	STORAG_TANKS	RECEIVE PRODUCT	RECEIVE PRODUCT	AGITATE

Page 1

Figure 4. Print Preview of Simplified Procedure Report for Non-PostScript Printer

## PRODUCTION INFORMATION MANAGEMENT

Production information management comprises:

- ▶ Batch Server for Batch History and Reporting functions
- ▶ Historian
- ▶ Batch, Equipment, and Security History
- ▶ Historian Archive Function
- ▶ Process Logger
- ▶ Reporting System

## Batch Server

InBatch software uses a separate Batch server for Batch History and Reporting functions (refer to Figure 5).




Figure 5. Batch System Architecture

The Batch Server maintains a history cache to ensure no loss of historical data in the event of a temporary communications failure.

Historian

Comprehensive batch, equipment, and security history and flexible real-time reporting are hallmarks of InBatch software. The Batch Historian uses Microsoft SQL Server to store batch history information.

Batch, Equipment, and Security History

InBatch software provides the most comprehensive batch historian available, capturing all Electronic Batch Record (EBR), equipment, and security events.

- EBR events are the event data the Batch Manager captures and logs to the Batch Historian when batches are executing (refer to Figure 6). All these events are stored with time, date, and batch ID for easy retrieval.




Figure 6. Batch History (EBR)

- Equipment events occur each time the status of a piece of equipment changes, and the Batch Manager captures and logs the change to the Batch Historian (refer to Figure 7). All these events are stored with the old status, new status, current recipe ID, and last recipe ID.




Figure 7. Equipment History

- Security events occur whenever the Batch Manager captures and logs security events to the Batch Historian (refer to Figure 8). Configuration edits include security database changes such as deleting a user and changing a user's password.




Figure 8. Batch Security History

History Archive Function

The History Archive function allows you to create, edit, and execute archiving tasks that are registered by SQL Server. You identify the starting point and the ending point for archiving history data. The dates are inclusive, that is, all batches completed on or after the starting date and all batches completed on or before the ending date are archived. A batch is considered completed when it has obtained a status of Done or Aborted, and is closed (removed from the batch schedule). After an archive has been created, it can be deleted, restored or purged.

Process Logger

The Process Logger retrieves data and passes it to the printer or to the Batch Suite Historian for storage. The Process Logger Editor window creates data collection configurations, which consist of one or more groups of tags with each group having its own data collection configuration. The run-time Process Logger uses the logging configuration to determine how each group of tags and its respective values should be collected and logged. Data collection may be periodically scheduled or event driven.

## Reporting System

With InBatch software, real-time reporting capabilities are available using Archestra Reports within Wonderware Information Server (WIS), leveraging Microsoft Reporting Services capabilities for configuring reports and WIS for viewing reports.

Be aware that WIS Client licenses are required for viewing published reports on workstations in a network.

Reports are available to any workstation equipped with a network connection (a second Ethernet connection is required), a valid WIS license, and an

Internet browser. The reporting system offers end-of-batch reports and time triggers, such as time of day. Both batch and continuous data can be combined in one report.

InBatch software provides more than 20 report templates as examples for your use. You can run and view reports using the WIS interface as shown in Figure 9.

Reports can retrieve any piece of information stored in the Batch Historian and can be used in a real-time or off-line mode. Refer to Figure 10.




Figure 9. Batch Reports Interface via Wonderware Information Server (WIS)




Figure 10. Sample Batch Journal Report

Examples of Batch report templates are:

- ▶ A listing of I/A Series analog alarms issued for a batch (if installed with I/A Series components)
- ▶ A summary of all batch execution activity for a batch
- ▶ A summary of all questions for a batch
- ▶ A listing of I/A Series Boolean alarms issued for a batch (if installed with I/A Series components)
- ▶ A summary of all material characteristics for a campaign, lot and batch
- ▶ A summary of the changes made by operators to the original formula input quantities for a batch
- ▶ A summary of all materials consumed in a batch

- ▶ A summary of all materials produced by a batch
- ▶ Totals of all materials produced for a batch
- ▶ A summary of all operator comments for a batch
- ▶ A summary of all recipe phase instructions for a batch
- ▶ A summary of all process log values for a batch
- ▶ Statistical information of all process log values recorded for a specific tag
- ▶ A summary of all process variable target and actual values for a batch
- ▶ A summary of changes made by operators to the original formula process variables for a batch
- ▶ A listing of I/A Series sequence block messages issued for a batch (if installed with I/A Series components)
- ▶ A list of batches that used a specific material or material from a specific vendor
- ▶ A summary report of all batches produced
- ▶ A summary report of all equipment status changes
- ▶ A summary of all finished products produced
- ▶ A summary report that includes the number of finished products produced, number of lots, number of batches and total quantity produced.

## ENHANCED SECURITY OPTIONS

### Standard Batch Security

InBatch software provides a standard security mode which may be used to control the access and manipulation capability of users. A security role is assigned to users based on their job functions such as operators, supervisors, engineers, and so forth. Only one security role can be assigned to a given user. New security roles can be added to the security system at any time, and there is no limit to the number of roles that can be defined.

InBatch applications and their associated functions can be assigned security roles defining which groups of users can access an application and which groups can execute and verify the various functions available within that application. The Batch applications include Batch Display, Batch Scheduler, Process Model Editor, Recipe Editor, and so forth. Each application can be assigned one or more security access roles permitting groups of users to access the application. Applications can be added to the security system at any time.

The Batch software supports security for execution and verification of the functions available within an application. As an example, the Batch Display application includes functions such as Abort Batch, Allocate Equipment, Start Batch, Unit Hold, and so forth. Each function can be assigned one or more Done By and Check By security roles. More than one role can be permitted to perform or verify a function, for example, both operators and supervisors could be permitted to perform a function, but only supervisors could verify the function. Functions can be added to the security system at any time.

Recipe and operator station security assignments are made on a per user basis.

Recipe assignments protect against operators working on products for which they have not been trained. None, one, many, or all recipes can be assigned to a user. Security for the recipe delete function prevents an unauthorized user from deleting a master recipe.

Operator station assignments protect against operators working at operator stations to which they should not have access. None, one, many, or all operator stations can be assigned to a user.

Each user has an account consisting of a user name containing a maximum of 30 characters and a user identification containing a maximum of 12 characters. When a security clearance is required, the security system prompts the user for an ID and password.

The permitted number of requests for security clearance can be limited and access denied if the number of retries is exceeded by a user.

The system supports password time-out (the number of days a password is valid) and password reuse (the number of day which must pass before a password can be re-used). All passwords in the security system are stored and transmitted in an encrypted format.




Figure 11. InBatch Security Editor Configuration

### Operating System Batch Security

InBatch software provides an operating system batch security mode in which user authentication is performed against user data stored in the Windows operating system instead of in the InBatch security database. Users are selected from a list of configured users on the Windows operating system. For Operating System mode, a domain or local computer name is also required. If InBatch is used with I/A Series components, Operating System security mode is available when the InBatch software is installed on a system using the security enhanced I/A Series software v8.6 or v8.7.

### ArchestrA Batch Security

InBatch software provides an ArchestrA batch security mode in which user authentication is performed against user data stored in the ArchestrA galaxy and verified by Wonderware Application Server instead of in the InBatch security database. Users are selected from a list of configured users in the ArchestrA development environment.

ArchestrA security mode is not available when the InBatch software is installed with I/A Series components.

### User Access Activity Report

A report query template is provided to retrieve security administration and user access activity from history for display or printout.

### FDA 21 CFR Part 11 on Electronic Records and Electronic Signatures Regulation

InBatch software has been designed for use in validated processes that must comply with the FDA 21 CFR Part 11 on Electronic Records and Electronic Signatures. A white paper describing the regulation and how the Batch software helps users comply with the regulation is available.

## ENVIRONMENT MANAGEMENT SYSTEM

The Environment Management capability provides a controlled interface so you can monitor and manipulate the Batch Server applications and configurations in both the configuration and run-time environments. The Environment Management capability is configurable using the Environment Editor. The editor is used to define the applications that can run in the configuration or run-time environments and to set option switches for executables. The Environment display shows editor icons and run-time GUI-based applications that you can select and run. Additionally, you can start and stop background applications, monitor their status



and start and stop individual editor and display applications.

Listed below are the significant functions of the Environment Management capability:

- Copy Edit Model to Run Model
- Copy Run Model to Edit Model
- Start All Applications
- Stop All Applications
- Start Application
- Stop Application
- Edit Environment and Configure Applications Switches
- Update Environment
- Exit and Shutdown
- Exit.

## **PROGRAMMATIC INTERFACES TO INBATCH SOFTWARE**

These functions are included with the Batch Server license at no additional charge.

### **ActiveX Controls**

InBatch software four categories of ActiveX controls that provide access to runtime batch information. You can use these to develop custom batch interface applications within COM-based environments such as Visual Studio and Wonderware InTouch.

#### **Batch SFC ActiveX Control**

The Batch SFC ActiveX control (InBatchSFC.ocx) enables the runtime sequential function chart representation of an active batch to be used in the container application. This SFC is the same as shown on the Batch Display application.

#### **Batch ActiveX Control**

The Batch ActiveX control (OcxBatch.ocx) provides access to the runtime schedule and display information for active batches. You use this control to develop custom applications that provide the following functionality:

- Add, change, and delete batch schedule data
- View, select, and control current active batches
- View and modify active and inactive phases and parameters for a running or scheduled batch
- View and modify phase properties for a running batch
- View and answer questions for a running batch
- View and change equipment allocation data for a running batch
- View and force active transition logic expressions for a running batch
- View batch errors and batch messages

### **Batch GUI ActiveX Controls**

The Batch GUI ActiveX controls (GUIControls.dll) are a collection of four controls (configuration, batch field, batch list, and batch button) that provide access to the runtime schedule and display information for active batches. The GUI controls are pre-defined controls that can be used to easily assign any available batch field, list, or button behavior to the control instance. These controls can be used to very quickly and easily develop a custom batch user interface application.

### **Batch Security ActiveX Control**

The Batch Security ActiveX control (BatchSecCtrl.dll) provides access to the standard InBatch security system including application and function security clearance.

### **COM Automation Servers**

InBatch software includes two Automation Servers that provide access to the material and the recipe databases. Each server is comprised of a set of object classes that contain a variety of methods and properties. You can use these to develop custom applications within COM-based environments such as Visual Studio™.

### Materials Database Automation Server

The Materials Database Automation Server (MaterialSrv.exe) provides read and write access to the materials database. You use the server to develop custom applications that provide the following functionality:

- ▶ Add, change, and delete materials (ingredients, intermediates, etc.)
- ▶ Define default characteristics for a material
- ▶ Query and assign available units to a material
- ▶ Add and remove lot tracking information for a material assigned to a unit
- ▶ Query material lot tracking information
- ▶ Define actual characteristic values for a specific lot of material
- ▶ Find the location of a material
- ▶ Query the contents of a unit
- ▶ Query the total quantity of a material.

### Recipe Database Automation Server

The Recipe Database Automation Server (RecipeEdit.exe) provides read and write access to the recipe database. You use the server to develop custom applications that provide the following functionality:

- ▶ Add, change, and delete recipes
- ▶ Query and change recipe header information
- ▶ Query and change recipe equipment requirements
- ▶ Query formula inputs defined for a recipe
- ▶ Query formula outputs defined for a recipe
- ▶ Define and modify the formula for a recipe
- ▶ Define a recipe procedure.

### Batch Function Interface Libraries

InBatch software includes two type libraries that define an interface from which you can create an in-process server (dll) to interact with the batch function interface. Each type library is comprised of a set of object classes that contain a variety of methods and properties. You can use these to develop custom servers with COM-based environments such as Visual Studio.

The Batch Hooks Type Library (*batchvbserver.dll*) includes functions and subroutines that can be used to access the batch function interface. The batch function interface consists of several hooks into the execution of Batch Manager. Adding logic to these hooks allows you to extend the capabilities of Batch Manager.

The Batch Object Type Library (*batchobjsrv.dll*) provides objects that contain the appropriate batch, phase, parameter, and equipment data available and modifiable within the hooks.

### Stateless Application Programming Interface (API)

InBatch includes a stateless API that contains many of the functions available in the Batch ActiveX Control. This API can be referenced within Visual Studio and within ArchemstrA application objects developed using the ArchemstrA Integrated Development Environment (IDE) and InBatch without I/A Series Components (FCS). You use this API to provide the following functionality:

- ▶ Add, delete, and query batch schedule data
- ▶ Select and control current active batches
- ▶ Allocate and release equipment
- ▶ Query batch security configuration.

## **UPGRADING TO INBATCH SOFTWARE**

Information about migration of Model, Recipe, Material, Link, Logger, and Security databases to InBatch 9.5 with SP1 for previous versions of I/A Series Batch and InBatch software is available upon request. Contact Global Client Support (GCS) for additional information.

## **I/A SERIES INTEGRATION**

Associations between equipment and a batch are dynamically made in the control package so that any batch related alarm messages contain the Batch ID. This ensures data integrity when queries are made later on the Batch Historian and obviates the need to infer associations between equipment and a batch based on time.

Using the Batch display for a given batch, you can launch FoxAlert software with match filtering automatically set to the Batch ID of that batch. This ensures that only those alarms that pertain to that batch are displayed in this view (refer to Figure 12).

Phase and formula parameter descriptions are available from the Batch display.

Phase logic is implemented using I/A Series sequence blocks. The use of the companion product, I/A Series SFC software, allows these sequence blocks to be configured and displayed in a graphical format that follows the IEC 61131-3 standard. When viewing a phase from the Batch display, you can launch the SFC/ST display for that phase (if it was configured using the SFC/ST Configurator) to quickly and easily determine, via highlighting, where you are in that phase and to view the live, updating evaluation of any active transitions (refer to Figure 12). This greatly reduces the time to debug and commission phase logic as well as provides a handy tool to operations people for ongoing support.




Figure 12. Integration with Alarm Alert and SFC/ST Display Manager

When installed without the I/A Series components, InBatch software is still well integrated with the rest of the I/A Series platform, but the integration is done using the Foxboro Control Software (FCS) rather than the integration options described above.

Communication to the I/A Series control system is done using the I/A Series Device Integration Object (IADI) and/or the I/A Series Data Access Server (IADAS).

## ARCHESTRA (FCS) INTEGRATION

When installed without the I/A Series components, InBatch software includes several features for tightly integrating the software to the rest of the Archedra or FCS infrastructure including I/A Series software. Batch tags can be linked to the galaxy repository and a new communication software module (IBMX) is available to communicate with Archedra rather than directly to the control system. Archedra objects and attributes can be browsed and assigned within the batch tag linker application. Standard batch security can be enhanced to support operating system or Archedra security. In addition, the ActiveX controls can be used to develop a tightly integrated human machine interface if using Wonderware InTouch or FCS InTouch Application software.

## BATCH SYSTEM CONFIGURATION

The InBatch system is comprised of several components including Batch Server, Runtime Client, Development Client, History Server, Reporting Content. A utility is used to configure each component. See Figure 13.

The InBatch server is scalable and available in three sizes: large, medium, and small. The number of runtime and development stations is selectable.

The Batch Server license includes the Runtime Client and the Development Client functionality, giving access to all product capabilities from the Batch Server workstation. Additional Runtime and Development clients may be installed on other workstations as required.

The History Server and Reporting Content can be installed on one workstation or split onto two different workstations.




Figure 13. InBatch Configuration Utility

### Redundant Batch Server Option

Batch Server redundancy capabilities allow the server to automatically switch batch control to a backup server in the event of a primary server shutdown due to a hardware failure or power loss. Two identical servers are required to configure a redundant system (refer to Figure 14).




Figure 14. Batch Server Redundancy

## InBatch Software and Terminal Services

InBatch software supports terminal services for batch Runtime and Development clients. The batch client terminal services software must be installed and licensed on a server other than the Batch server. See Figure 15.




Figure 15. InBatch Software and Terminal Services

## ETHERNET NETWORKS

Ethernet networks (in addition to The Mesh control network) are required between the Batch Server and Batch Clients. Refer to Figure 16.

## BATCH SERVER

The Batch Server for Batch History and Reporting functions rely heavily on resource-intensive SQL Server, Internet Information Server, and Wonderware Information Server (WIS). This requires a powerful computer.

## Operating System Considerations

The Batch server for Batch History and Reporting functions is deployed on a supported platform - refer to Table 2 on page 26.

## Hardware Considerations

When evaluating the hardware for use with the Batch server that will be performing Batch History and Reporting functions, you should consider failure of the disk drive, network interface card, and power supply.

Disk subsystems (controllers/disk) should use Serial Attached SCSI (SAS) or Serial ATA (SATA) interfaces, and should ideally be a hardware RAID. When RAID configurations are not used, the SAS and SATA interfaces provide a level of fault tolerance, since the Windows operating system dynamically relocates detected disk errors to good sectors.

SQL Server, a significant disk resource consumer, also has specific system requirements that necessitate separate hard drives for the database and database log for recovery purposes.






Figure 16. Batch Reporting System Configuration

### Basic Production System

For a minimum configuration, disregarding fault resilience and performance concerns, the following platform is sufficient: a current Intel® compatible processor, 2 GB memory, three SAS or SATA disk drives (OS, database, and database logs), and an optional tape or R/W DVD drive.

### Power Production System

Multiple processors help to ensure processor availability during extreme non-OLTP (On-Line Transaction Processing). Reporting demands can change the processor requirements dramatically.

A RAID configuration utilizing two disk drives at RAID1 and four drives at RAID5 is ideal. The operating system, application software, and database logs are on mirrored drives (RAID1).

The database is on three drives at RAID5 with data parity striped across all drives. For additional performance, RAID10 can be used. A hot spare drive (RAID5) is included to rapidly recover from reduced performance and to increase availability.

## BATCH SOFTWARE FUNCTIONAL SPECIFICATIONS

### Process Model

There are no absolute limits on the number of process units or connections. The only limitation is hard disk space in the host processor.

### Maximum Number of Formula Variables per Phase when Downloading to an I/A Series Sequence Block

24 booleans, 8 integers, 15 reals and 10 strings  
{Note: These limitations do not apply when downloading to multiple blocks.}

### Maximum Number of Recipes

Unlimited. The only limitation is hard disk space in the host processor.

### Maximum Number of Serial Steps (Operations) in a Recipe

510

### Maximum Number of Serial Steps (Phases) in an Operation

510

### Maximum Number of Phases for Operator Selection of Parallel Execution

20

## RECOMMENDED MINIMUM HARDWARE REQUIREMENTS

The following hardware is recommended to support InBatch v9.5 with SP1:

- ▶ Processor: 3.0 gigahertz (GHz) or faster processor
- ▶ RAM: 2 gigabyte (GB) of memory
- ▶ Hard disk: At least 4 GB of available disk space
- ▶ Video adapter and monitor with super VGA (1024 × 768) resolution or higher

- ▶ CD-ROM or DVD drive for installation

- ▶ Keyboard

Mouse or compatible pointing device

Refer to your specific Microsoft operating system hardware requirements for details.

## I/A SERIES SOFTWARE COMPATIBILITY

InBatch v9.5 with SP1 is compatible and can co-exist with the following products:

- ▶ ArchestrA System Platform 2012
- ▶ Wonderware Application Server 3.5
- ▶ Foxboro Control Software v3.0 and v3.1
- ▶ I/A Series Software v8.4.3, v8.5, v8.6 and v8.7
- ▶ Wonderware InTouch® 10.5
- ▶ Wonderware Historian 9.0 P02 and 10.0 SP1
- ▶ Wonderware Historian Client 10.0 SP1 and 10.0 SP2
- ▶ Wonderware Information Server 4.0 and 4.5

- ▶ DIObjects 4.1 SP2

You must install Microsoft .NET Framework 3.5 SP1 before installing Wonderware InBatch 9.5 with SP1. If this version of the .NET Framework is not installed on the station, the Wonderware InBatch installation automatically installs it.

Refer to the following tables for more specific requirements.

Table 1. InBatch V9.5 with SP1 Software Operating System Requirements for I/A Series Stations

Operating Systems		Service Pack Level	InBatch Features					
			Server	Run-time Client	Development Client	History Server	Reporting Content	Redundant System
H90/H91 or P90/P91 Windows Server 2003 R2	32-bit only	SP2	Yes	Yes	Yes	Yes	-	Yes
H92 or P92 Windows XP	32-bit only	SP3	Yes	Yes	Yes	-	-	Yes

## OPERATING SYSTEM SOFTWARE COMPATIBILITY

Table 2. InBatch V9.5 With SP1 Software Operating System Requirements for Off Platform Stations

Operating Systems		Service Pack Level	InBatch Features					
			Server	Run-time Client	Development Client	History Server	Reporting Content	Redundant System
Windows Server 2003 R2 Standard	32-bit only	SP2	Yes	Yes	Yes	Yes	Yes	Yes
Windows Server 2003 R2 Enterprise	32-bit only	SP2	Yes	Yes	Yes	Yes	Yes	Yes
Windows Server 2008 Standard	32-bit & 64-bit	SP2	Yes	Yes	Yes	Yes	Yes	Yes
Windows Server 2008 Enterprise	32-bit & 64-bit	SP2	Yes	Yes	Yes	Yes	Yes	Yes
Windows Server 2008 R2 Standard	32-bit & 64-bit	SP1 <sup>(a)</sup>	Yes	Yes	Yes	Yes	Yes	Yes
Windows Server 2008 R2 Enterprise	32-bit & 64-bit	SP1 <sup>(a)</sup>	Yes	Yes	Yes	Yes	Yes	Yes
Windows Vista Business	32-bit & 64-bit	SP2	Yes	Yes	Yes	Yes	Yes	Yes
Windows Vista Enterprise	32-bit & 64-bit	SP2	Yes	Yes	Yes	Yes	Yes	Yes
Windows Vista Ultimate	32-bit & 64-bit	SP2	Yes	Yes	Yes	Yes	Yes	Yes
Windows XP Professional	32-bit only	SP3	Yes	Yes	Yes	No	No	Yes
Windows 7 Professional	32-bit & 64-bit	SP1 <sup>(a)</sup>	No	Yes	Yes	No	Yes	Clients only
Windows 7 Enterprise	32-bit & 64-bit	SP1 <sup>(a)</sup>	No	Yes	Yes	No	Yes	Clients only

(a) Supported with and without Service Pack.

**NOTE**

For InBatch add-on for Win-XML Exporter software requirements, refer to the software requirements for Wonderware Information Server.

For InBatch IDE/FCS Configuration Tools Extension software requirements, see software requirements for Wonderware Application Server.

**MICROSOFT SQL SERVER SOFTWARE COMPATIBILITY**

**Table 3. InBatch V9.5 With SP1 Software Microsoft SQL Server Database Requirements**

Version	Type	Service Pack Level
Microsoft SQL Server 2005	Standard or Enterprise Edition	SP3
Microsoft SQL Server 2008	Standard or Enterprise Edition	SP1, SP3(a)
Microsoft SQL Server 2008 R2	Standard or Enterprise Edition	-

(a) Check if other products that use the same operating system as InBatch 9.5 with SP1 are compatible with Microsoft SQL Server 2008 SP3.

**I/A SERIES ADDITIONAL SOFTWARE COMPATIBILITY**

**Table 4. InBatch V9.5 With SP1 Software Additional Software Requirements for Each I/A Series Station Type**

Additional Software Requirements	InBatch Features					
	Server	Run-time Client	Development Client	History Server	Reporting Content	Redundant System
Foxboro Control Software v3.0 and v3.1 (with I/A Series Software 8.7)	Yes	-	-	-	-	Yes
I/A Series Software v8.6 and v8.7	Yes	-	-	-	-	Yes
Foxboro Control Software 3.1 FCS InTouch Application	-	Yes	-	-	-	-
Foxboro Control Software 3.1 FCS Configuration Tools	-	-	Yes	-	-	-
Internet Information Services (IIS) 6.0 or 7.0	-	-	-	Yes	-	-
Wonderware Information Server with ArchestrA Reports Feature	-	-	-	-	Yes	-

**Table 5. InBatch V9.5 With SP1 Software Additional Software Requirements for Each InBatch Station Type**

Additional Software Requirements	InBatch Features					
	Server	Run-time Client	Development Client	History Server	Reporting Content	Redundant System
Wonderware Application Server bootstrap and IDE (only when integrating with System Platform and FCS)	Yes	-	Yes	-	-	-
Wonderware InTouch 10.1 or higher	-	Yes	-	-	-	-
Internet Information Services (IIS) 6.0 or 7.0	-	-	-	Yes	-	-
Wonderware Information Server with ArchestrA Reports Feature	-	-	-	-	Yes	-

## INBATCH VERSION 9.5 SOFTWARE PART NUMBERS

The following tables list the software license part numbers, Batch Backup Server part numbers, and related product part numbers.

**Table 6. InBatch V9.5 Software License Part Numbers**

Part Number	Title	Description
62-0112	Wonderware InBatch v9.5 Server Large	Wonderware InBatch v9.5 with SP1 supports the H9x/P9x family of workstations and I/A Series software v8.6-8.7 releases. Wonderware InBatch can be used standalone or with the Foxboro Control Software (FCS). This Batch Server license is for unlimited units. All Batch Servers include: Operator/Runtime Client and Configuration/Development Client capabilities (local use), Batch Server for History and Reporting functions based on Microsoft SQL Server, Wonderware Information Server for all reporting, (1) WW Basic CAL which includes (1) Microsoft SQL Server CAL, (1) Information Server Advanced Client (local use).
62-0113	Wonderware InBatch v9.5 Server Medium	Wonderware InBatch v9.5 with SP1 supports the H9x/P9x family of workstations and I/A Series software v8.6-8.7 releases. Wonderware InBatch can be used standalone or with FCS. This Batch Server license is for 16-40 units. All Batch Servers include: Operator/Runtime Client and Configuration/Development Client capabilities (local use), Batch Server for History and Reporting functions based on Microsoft SQL Server, Wonderware Information Server for all reporting, (1) WW Basic CAL which includes (1) Microsoft SQL Server CAL,(1) Information Server Advanced Client (local use).
62-0114	Wonderware InBatch v9.5 Server Small	Wonderware InBatch v9.5 with SP1 supports the H9x/P9x family of workstations and I/A Series software v8.6-8.7 releases. Wonderware InBatch can be used standalone or with FCS. This Batch Server license is for 1-15 units. All Batch Servers include: Operator/Runtime Client and Configuration/Development Client capabilities (local use), Batch Server for History and Reporting functions based on Microsoft SQL Server, Wonderware Information Server for all reporting, (1) WW Basic CAL which includes (1) Microsoft SQL Server CAL,(1) Information Server Advanced Client (local use).
62-0115	Wonderware InBatch v9.5 RedSvr Large	This license supports a redundant InBatch Server for unlimited units. This license requires that you have part 62-0112, Wonderware InBatch v9.5 Server Large in place.



Table 6. InBatch V9.5 Software License Part Numbers (Continued)

Part Number	Title	Description
62-0116	Wonderware InBatch v9.5 RedSvr Medium	This license supports a redundant InBatch Server for 16-40 units. This license requires that you have part 62-0113, Wonderware InBatch v9.5 Server Medium in place.
62-0117	Wonderware InBatch v9.5 Red.Svr Small	This license supports a redundant InBatch Server for 1-15 units. This license requires that you have part 62-0114, Wonderware InBatch v9.5 Server Small in place.
62-0118	Wonderware InBatch v9.5 Rt.Client	InBatch Runtime Client allows use of the Batch Client application, use of InBatch software ActiveX controls in an InTouch or third-party container application. InTouch software is purchased separately.
62-0119	Wonderware InBatch v9.5 DevClient	InBatch Development Client provides configuration capability for InBatch software on an additional workstation. It provides all batch editors including Model Editor and Recipe Editor and permits batch configuration from a remote client.
62-0120T	Wonderware InBatch v9.5 DevClient TSE	InBatch Development Client TSE is a Development license to use InBatch configuration client capability through a Terminal Server session. One license per session is required - the console counts as one session.
62-0121T	Wonderware InBatch v9.5 Rt.Client TSE	InBatch Runtime Client Terminal Services Edition (TSE) is a runtime license to use InBatch Client application and ActiveX controls on a Terminal Server (TS). One Runtime Client TSE license per session is required - the TS console counts as one session.
62-0121TF	Wonderware InBatch v9.5 Rt.Client TSEF	InBatch Runtime Client TSE Failover is a runtime license to use InBatch Client application and ActiveX controls on an additional Failover/Load balancing Terminal Server for high availability of Terminal Server based operator client concepts (order the same amount of RT failover clients as for primary Terminal Server).

**Table 7. Advantage Upgrade Part Numbers**

Part Number	Title
<p>Special Advantage pricing may be used for migrations from FoxBatch software and from previous versions of I/A Series Batch software or InBatch software. Advantage pricing on InBatch software licenses may also be extended to competitive migration projects. Contact Global Client Support (GCS) for additional information.</p> <p>Additionally, information about upgrading from all previous Invensys Batch products, including FOX 1/A™ Batch, EasyBatch™, Batch Plant Management, RBATCH™, and RBATCH II™ software is available upon request.</p>	
P0998EY	Advantage for Wonderware InBatch v9.5 With SP1 Server Large
P0998EZ	Advantage for Wonderware InBatch v9.5 With SP1 Server Medium
P0998FA	Advantage for Wonderware InBatch v9.5 With SP1 Server Small
P0998FB	Advantage for Wonderware InBatch v9.5 With SP1 RedSvr Large
P0998FC	Advantage for Wonderware InBatch v9.5 With SP1 RedSvr Medium
P0998FD	Advantage for Wonderware InBatch v9.5 With SP1 Red.Svr Small
P0998FE	Advantage for Wonderware InBatch v9.5 With SP1 Rt.Client
P0998FF	Advantage for Wonderware InBatch v9.5 With SP1 Rt.Client TSE
P0998FG	Advantage for Wonderware InBatch v9.5 With SP1 Rt.Client TSEF
P0998FH	Advantage for Wonderware InBatch v9.5 With SP1 DevClient
P0998FJ	Advantage for Wonderware InBatch v9.5 With SP1 DevClient TSE
P0998FK	Information Server Standard Client Named Device v4.0

**Table 8. Related Product Part Numbers**

Part Number	Title	Description
J0200LA	I/A Series SFC Software License (70 Series)	The SFC software comprises the Sequential Function Chart and Structured Text (SFC/ST) Configurator and Display Manager for I/A Series sequence blocks. This includes SFC/ST sequence block displays which may be viewed from any workstation hosted by the workstation where I/A Series SFC resides. SFC runs on I/A Series Windows platforms at Version 6.2 and higher. One SFC license is required for each instance of the I/A Series Integrated Control Configurator (ICC).

Invensys Operations Management  
5601 Granite Parkway Suite 1000  
Plano, TX 75024  
United States of America  
<http://iom.invensys.com>

Global Customer Support  
Inside U.S.: 1-866-746-6477  
Outside U.S.: 1-508-549-2424 or contact  
your local Invensys representative.  
Website: <http://support.ips.invensys.com>

Invensys, AIM\*AT, FoxAlert, FoxAPI, FoxBatch, FoxView,  
I/A Series, InFusion, InTouch, Wonderware, and the  
Invensys logo are trademarks of Invensys plc, its  
subsidiaries, and affiliates.  
All other brands and product names may be the  
trademarks of their respective owners.

Copyright 2004-2012 Invensys Systems, Inc. All rights  
reserved. Unauthorized duplication or distribution is strictly  
prohibited.