

SCD5200 Input/Output Modules



OVERVIEW

The SCD5200 Input/Output Modules provide connection of wide range of field equipment and devices to the SCD5200 Station Computing Devices for monitoring and control of industrial plant.

The SCD5200 range of I/O modules comprises:

- ▶ Multi I/O Module
- ▶ Analog Digital Input (ADI) Module
- ▶ 20 Channel Analog Input Module
- ▶ 4 Channel Analog Output Module
- ▶ Digital Output Module.

Field Interrogation Power Supply (FIPS) options for digital inputs include nominal 24 V to 129 V, selectable via jumper settings.

A 1 kV isolation option is available for the analog inputs on the Analog Digital Input (ADI) Module and 20 Channel Analog Input Module.

Latched and non-latched relay options are available on Digital Outputs.

Key features of the range include:

- ▶ Opto-isolated digital inputs
- ▶ Relay-isolated digital outputs
- ▶ High isolation optional on analog inputs
- ▶ Analog outputs individually isolated
- ▶ High security “check-before-operate” control outputs
- ▶ Sequence of Events resolution of 1 ms
- ▶ High resolution analog inputs (12 bit plus sign) and analog outputs (12 bit)

- ▶ Digital inputs provide Status, Momentary Change Detect, Accumulator, and Sequence of Events
- ▶ Software configurable
 - Digital outputs as individual variable pulse or latched, trip/close or raise/lower pairs, multiple relay variable pulsed or latched
 - Analog output range and offset, open loop detection
- ▶ High transient and surge immunity
- ▶ EMC emission and immunity to CE standards for industrial equipment
- ▶ Analog current loop resistors integral to terminal boards
- ▶ Enclosed insulated terminal assemblies for safety
- ▶ Removable terminal assemblies allow card replacement without disconnecting field wiring
- ▶ Run/fail status front panel indicator and database health point
- ▶ High density for compact connection of large I/O count
- ▶ Range of I/O combinations provides connection flexibility at minimum cost.

Through flexible I/O configurations and options, the range of SCD5200 I/O Modules is matched to a wide range of applications.

The combination of a ten I/O module capacity file, integrated local network capability, and high I/O density modules can accommodate large to very large I/O counts while providing excellent value for money.

The one I/O card file and five I/O card file options (Refer PSS 31H-8G1 SCD5200 Architecture Overview) aim to meet the needs of small I/O and space limited applications.

The Multi I/O Module provides the highest I/O density of combined digital input, analog input, and digital output (24 DI, 6 AI, and 6 or 8 DO). The ADI Module (32 DI and 4 AI) provides for high density input-only configurations.

Where greater flexibility of configuration, connection, and/or isolation is required, the Analog Input Modules, Analog Output and Digital Output Modules may be combined with the high density Multi I/O and ADI Module types.

As the modular design of the SCD5200 allows any mix of I/O modules, a wide range of number and type of I/O connections may be economically accommodated.

The I/O module range is designed and tested for application in the most demanding industrial environments. Compliance standards include European Community (CE) Electro-Magnetic Compliance (EMC) immunity and emissions, transient and surge immunity, isolation, and electrical safety. CE Mark certification and CE compliant installation guidelines are available.

Software complements the I/O module hardware. Momentary Change Detect, Sequence of Events, and Accumulator functionality is provided for digital inputs. Digital outputs are highly secure, incorporate “check before operate” execution, and may be configured as variable pulse, latch, trip/close pairs, or multiple relay groups (set point).

FUNCTIONAL DESCRIPTION

Analog/Digital Input Modules

The Analog/Digital Input Module provides flexible data collection and input monitoring facilities through 32 individually configured digital inputs and four high-resolution analog inputs.

The Analog/Digital Input Module has 1 kV isolation on the analog inputs.

The module supports digital inputs over the nominal ranges of 24 V to 48 V and 48 V to 129 V. A jumper for each digital input can be individually set to select either of these ranges. The factory default setting is for 48 V to 129 V operation.

WARNING

In this module, the jumpers J3 to J34 must be removed when using digital input voltages in the range 60–129 V (dc) or 72–144 V RMS (ac). Failure to do so may result in permanent damage to the module and possible electric hazard.

Features

Key features of the ADI Modules include:

- ▶ Removable plug-connected terminal board
- ▶ Plug in current loop resistors
- ▶ Software configurable digital inputs
- ▶ Optical isolation on digital inputs
- ▶ Galvanic isolation on analog inputs
- ▶ Common voltage inputs (+VE or -VE) that are selectable in groups of eight digital inputs
- ▶ Digital input bounce elimination circuitry
- ▶ Individually configurable chatter filters
- ▶ RUN/FAIL LED indicator.

NOTE

The Analog/Digital Input Module is available in two variants to support two different sizes of wires in terminal assembly. The size of the wire is based on insulation requirements, that is, thicker wires are required to support higher insulation requirements.

SY-0399160 accommodates wire sizes of 0.5 sq.mm and SY-039922 accommodates wire sizes of 1sq.mm.

The thickest wire size supported for a fully populated IO count [45 wires] is 0.75 sq.mm for the SY-0399160 and 1.0 sq.mm for the SY-039922. In all other respects, SY-039922 is identical to SY-0399160.

Digital Inputs

The digital input subsystem processes 32 contact inputs. The module optically isolates, filters, and protects against surge transients. It interfaces the contact state to the on-board microprocessor.

Digital input circuits employ contact bounce elimination circuitry, which rejects noisy contact transitions until the input signal has been stable for 2 ms.

The digital inputs are grouped into four groups of eight, with a common terminal for each group. Each group accepts common positive or common negative.

Digital inputs status is provided by scanning every millisecond. Sequence of Events with one millisecond resolution time-tagging is available.

In addition, each of the digital inputs supports accumulator and Momentary Change Detection functionality.

Analog Inputs

The analog input subsystem consists of individually isolated amplifiers and analog-to-digital converters for each input. Each input is measured and converted to a 12-bit plus sign value and has automatic zero drift correction and calibration scale checking. The conversion provides a nominal range of values from -4000 to +4000 for inputs from -2V to +2V with overrange capability to ± 2.0475 Volts. The plug-in current loop termination resistor value for each input is selected so as to provide a 2 Volt signal for the nominal full-scale current loop range.

12 Channel Digital Output Modules

Two versions of the output module are available:

- ▶ 12 Pilot Relay Output Module
- ▶ 12 Magnetically Latched Relay Output Module

The SCD5200 12 Channel Digital Output Modules offer several configuration possibilities. Relay outputs can be configured as individual relays, pairs, or

multiples in set point combinations. Two-pass operation with built-in hardware checking ensures reliable control over equipment.

Features

Key features of the Digital Output Modules include:

- ▶ 12 independent relays
- ▶ Magnetically latched relays are optional
- ▶ RUN/FAIL LED indicator
- ▶ Module operating condition available as RTU database point
- ▶ Configurable output types (latch, variable pulse, trip/close pairs, raise/lower pairs, and multiple relays)
- ▶ High security control output logic with two pass ‘check before operate’
- ▶ Built-in hardware and software monitoring of control operations
- ▶ Removable plug-connected termination assembly
- ▶ Control output duration is individually configurable.

Module Description

The SCD5200 digital output subsystem provides security and control for twelve electrical or magnetically latched relays. The 12 Channel Digital Output Modules consist of an on-board microprocessor and security circuits mounted on a logic board with a plug-in relay and terminal assembly. Configuration data from the main processor (COPE) determines the control of each output relay by the on-board processor.

Digital Output Subsystem

The 12 Channel Digital Output Module contains source and sink drivers for 12 relays. Each relay may be driven as fixed length pulse outputs, variable length pulse outputs, or latched outputs.

Two-Pass Operation

During pass 1, the on-board microprocessor accepts command data from the main processor (COPE). The

validity of the command is confirmed and then the hardware is checked on the output driver circuits. If tests succeed, feedback of the command is sent to the main processor.

During pass 2, the main processor (COPE) sends the execute command and the control relays are operated. Pulse output controls are automatically timed and independently checked.

8 Channel Digital Output Module

The 8 Channel Digital Output 10A Module provides high current AC and DC control outputs at voltages up to 129V dc and 110 Vac. High switching capacity relays are used to provide long contact life while controlling inductive loads up to 129 V dc nominal.

Features

Key features of 10A Digital Output Modules include:

- ▶ Eight independent single pole normally open digital outputs
- ▶ Two power relays in series provide high current DC inductive load break capacity
- ▶ Configurable output types (latch, variable pulse, trip/close pairs, raise/lower pairs, and multiple relays setpoint)
- ▶ High security control output logic with two pass ‘check before operate’ and one-of-N check on paired outputs
- ▶ Built-in hardware and software monitoring of control operations
- ▶ Removable plug-connected termination assembly
- ▶ Control output duration is individually configurable
- ▶ Screw terminals for loop connection of up to 16 gauge cable.
- ▶ RUN/FAIL LED indicator
- ▶ Module operating condition available as database point.

Module Description

The SCD5200 digital output subsystem provides security and control for electrical or magnetically latched relays. The Digital Output Modules consist of an on-board microprocessor and security circuits mounted on a logic board. Configuration data from the main processor (COPE) determines the control of each output relay by the on-board processor.

For the 10A relay modules, the relays are mounted on the logic board. The plug-in terminal assembly carries screw terminals for loop termination of heavy gauge wire.

Multi Input/Output Module

The SCD5200 Multi I/O Module provides a cost effective solution for applications utilizing a combination of status inputs, analog inputs and control outputs.

The SCD5200 Multi I/O Module combines the technology of the Analog Digital Input Module and the 12 Digital Output Module within one module:

- ▶ 24 Digital Inputs
- ▶ 6 Analog Inputs
- ▶ 8 mini pilot relay or 6 paired pilot relay outputs.

Variants of the SCD5200 Multi I/O Module are:

- ▶ 129 V 8 Mini Pilot Relay
- ▶ 48 V 8 Mini Pilot Relay
- ▶ 24 V 8 Mini Pilot Relay
- ▶ 129 V 6 Paired Pilot Relay
- ▶ 48 V 6 Paired Pilot Relay
- ▶ 24 V 6 Paired Pilot Relay.

Features

Key features of the Multi I/O Module include:

- ▶ Removable plug-connected termination assembly
- ▶ RUN/FAIL LED indicator
- ▶ Module operating conditions available as database points

Digital Inputs

- 24 software configurable digital inputs
- Individually configurable chatter filters
- Digital input bounce elimination circuitry
- Optical isolation on digital inputs
- Digital input common may be positive or negative.

Analog Inputs

- 6 analog inputs
- Plug-in current loop resistors
- 12 bits plus sign analog-to-digital converter
- ±2 V range
- Continuous automatic input calibration/check.

Control Outputs

- 8 mini pilot relays or 6 paired pilot relays
- Configurable output types (latch, variable pulse, trip/close pairs, raise/lower pairs, and multiple relays)
- Built-in hardware and software monitoring of control operations
- High security control output logic with two pass 'check before operate'.

Control output duration is individually configurable.




Figure 1. Multi I/O Module

Digital Inputs

This subsystem optically isolates, filters, protects against surge transients, and processes 24 status inputs. Digital input circuits rejects contact noise by use of contact debounce circuitry. Processing by the on-board microprocessor allows identification of chattering contacts.

The digital inputs share a pair of common terminals, which may be connected to positive or negative supply.

Digital inputs status is provided by scanning every millisecond. Sequence of Events with one millisecond resolution time-tagging is available.

In addition, each of the digital inputs supports accumulator and Momentary Change Detection functionality.

Analog Inputs

The analog input circuitry within the Multi I/O Module performs the data sampling and processing for the analog input points. This subsystem provides protection against surge transients, high frequency noise, and mains frequency noise. A multiplexed analog-to-digital converter provides high resolution and high-speed update of analog values.

These values are stored in shared memory for access by the main processor (COPE) via the Electrobus interface. Automatic zero drift correction is provided by the on-board microprocessor. Zero and full-scale voltage references are available as internal database points accessible by the SCADA Master Station.

Digital Outputs

The digital output subsystem of the Multi I/O Module provides secure control for the digital outputs. Eight mini pilot or six paired pilot relay options are available.

Outputs may be driven as fixed or variable length pulse, or may be electrically latched. Independent source and sink drivers control each output relay.

Two-Pass Operation

During pass 1, the on-board microprocessor accepts command data from the main processor (COPE). The validity of the command is confirmed and then the hardware is checked on the output driver circuits. If tests succeed, feedback of the command is sent to the main processor.

During pass 2, the main processor (COPE) sends the execute command and the control relays are operated. Pulse output controls are automatically timed and independently checked.

20 Channel Analog Input Module

The Analog Input Module provides a cost effective method for gathering a large volume of analog information from the field. The 20 Channel Analog Input Module provides accurate 12 bit plus sign resolution over wide temperature ranges. A 1 kV isolation option provides individually isolated channels.

In the non-isolated module, calibration values of zero and full scale voltage reference are available as database points while the isolated module utilizes a self-calibrating analog-to-digital converter.

Features

Key features of Analog Input Modules include:

- ▶ 20 analog inputs
- ▶ 12 bits plus sign analog-to-digital converter
- ▶ ± 2 V ranges
- ▶ RUN/FAIL LED indicator
- ▶ Plug-in current loop resistors
- ▶ Removable plug-connected termination assembly.

4 Channel Analog Output Module

The 4 Channel Analog Output Module provides four isolated current outputs. Outputs of 4 to 20, 0 to 10 and 0 to 16 mA are independently configurable.

Two-pass operation with built-in hardware checking ensures that reliable control of equipment is maintained. Each analog output can be scaled independently for the selected output current range as part of the RTU database configuration.

Features

Key features of Analog Output Modules include:

- ▶ Four channel analog output
- ▶ 12-bit resolution
- ▶ 4 to 20, 0 to 10, and 0 to 16 mA ranges
- ▶ Optical isolation of output circuits
- ▶ Internal monitoring of external voltage fail and open circuit alarms
- ▶ Removable plug-connected termination assembly.

Optical Isolation

The digital-to-analog converters are serially linked to the rest of the module via optical isolators. Power is supplied from an external source, which results in an electrically isolated interface to the external devices.

This design also sustains outputs, even in the event of RTU or module failure, providing external loop power is maintained.

Internal Monitoring

Each channel has two internal alarm points associated with it. If the external voltage source fails, or the current loop is open circuit to the output, the on-board processor is notified via optically isolated digital inputs. These inputs are then passed to the main processor (COPE) module, to be made available for scanning if required by the SCADA Master Station.

An operator can be notified if an analog device has been disconnected from the RTU, or if the external voltage source has failed, enabling problems in the field to be identified remotely.

MULTI I/O MODULE FUNCTIONAL SPECIFICATIONS**Multi I/O Module**

24 Status Input, 6 Analog Input, 8 mini-pilot or 6 paired pilot relay. (24 V, 48 V, or 129 V)

NUMBER OF CHANNELS

24 Status inputs
6 Analog field inputs
2 Internal check analog inputs
8 Mini-pilot relay controls or 6 paired pilot relay controls

ANALOG INPUTS

Input Circuit
6 differential inputs
Analog-to-Digital Converter Type
Sigma-Delta
Resolution
12 bits plus sign
Input Update Rate (Data Age)
<600 ms
Input Signal Range
±2 V dc
Input Signal Scaling
Dropping resistor for current inputs
Full Scale Range
±4000 counts (over range ±4095 counts)
Maximum Error at 25°C and 0 V Common Model
±0.1% full scale
Common Mode Error
0.01% per Volt to a maximum of ±6 V
Temperature Error
0.0016% per °C to over full temperature range
Maximum Error Over Temperature and Common Mode Range
±0.25% full scale
Differential Mode Rejection
80 dB at 6 V peak, dc to 50/60 Hz balance input
Differential Mode Voltage Without Damage
±50 V dc or peak ac
Common Mode Reject
60 dB minimum at 50/60 Hz

Maximum Common Mode Voltage

Operating within spec ±6 V
Without damage ±50 dc or peak ac

Transient Protection

IEEE C37.90-1
IEC 60255 Class 3
Impulse Voltage Withstand
Common mode 5 kV (input to ground)
Differential mode 5 kV (across input)
High Frequency Disturbance
Common mode 2.5 kV (input to ground)
Differential mode 1 kV (across input)
Fast Transient (IEC 61000-4-4)
4 kV 5 kHz capacitively coupled

Reference Voltages

Zero volts and full scale positive (+1 V)

DIGITAL INPUTS

Input Circuits
24 per input module
Input Types
Any input can be used as: Status, Momentary Change Detect, Sequence of Events, Accumulator
Circuit Types
Common return for all 24 inputs, positive or negative
Input Voltage
24 V, 48 V or 129 V dc from field supply
Input Current
5 mA per input (nominal)
Transient Protection
IEEE C37.90.1
IEC 60255 Class 3
Impulse Voltage Withstand
Common mode 5 kV (input to frame)
Differential mode 5 kV (input to common)
High Frequency Disturbance
Common mode 2.5 kV (input to frame)
Differential mode 1 kV (input to common)
Fast Transient (IEC 61000-4-4)
4 kV 5 kHz capacitively coupled
2 kV 5 kHz direct injection

MULTI I/O MODULE FUNCTIONAL SPECIFICATIONS (CONT.)

Multi I/O Module (Continued)

CONTROL OUTPUTS

Output Types

Outputs can be configured as: Pulse, Trip/Close pairs, Raise/Lower pairs, single Variable Pulse, Latched, or Set-point

Security

One or more than one relay energized test check before execution of control

Multi I/O Mini-Pilot Relay Termination

Assembly

24 V dc, 48 V dc, or 129 V dc with 2 kV ac RMS isolation to chassis for status inputs. Printed circuit assembly 261.8 mm x 35 mm attached to frame by captive screws. Terminals sized for 1.5 mm² wire.

ANALOG INPUTS

2 Terminals per point

Loop drop resistor mounted on rear side of terminal assembly

Suppression device to ground from each input terminal

DIGITAL INPUTS

24 status inputs

1 terminal per point

2 shared common terminals

Suppression device across each input to the common

MONITORS/INDICATORS

Green/Red RUN/FAIL LED

NUMBER OF RELAYS

Eight

RELAY COIL CURRENT

18 mA

CONTACT ARRANGEMENT

8 single pole contacts and 1 common

CONTACT RATING

0.5 A 125 V ac cos ϕ = 0.4 (30,000 operations)

D.C. make capacity

0.5 A 129 V dc (30,000 operations)

D.C. break capacity

0.25 A 50 V dc L/R 40 ms (30,000 operations)

50 mA 129 V dc L/R 40 ms (30,000 operations)

ISOLATION

2 kV RMS for 1 minute output to frame

1 kV RMS for 1 minute across open contact

TRANSIENT PROTECTION

IEEE C37.90.1

IEC 60255 Class 2

Impulse Voltage Withstand

Common mode 2.5 kV (output to frame)

Across output contact 1 kV

High Frequency Disturbance

Common mode 1 kV (output to frame)

Fast Transient (IEC 61000-4-4)

4 kV 5 kHz capacitively coupled

2 kV 5 kHz direct injection

Multi I/O Paired-Pilot Relay Termination

Assembly

24 V dc, 48 V dc, or 129 V dc with 2 kV ac RMS isolation to chassis for status inputs. Printed circuit assembly 261.8 mm x 35 mm attached to frame by screws. Terminals sized for 1.5 mm² wire.

ANALOG INPUTS

2 Terminals per point

Loop drop resistor and voltage divider terminals mounted on rear side of terminal assembly.

Suppression device across each input to the common

DIGITAL INPUTS

24 status inputs

1 terminal per point

2 common terminal

Suppression device across each input to its common

MONITORS/INDICATORS

Green/Red RUN/FAIL LED

NUMBER OF RELAYS

Six in 3 pairs

RELAY COIL CURRENT

18 mA

MULTI I/O MODULE FUNCTIONAL SPECIFICATIONS (CONT.)

Multi I/O Paired-Pilot Relay Termination Assembly (Continued)

CONTACT ARRANGEMENT

Contacts arranged as pairs of single pole contacts sharing a common

CONTACT RATING

5 A 250 V ac cos ϕ = 0.4 (30,000 operations)
D.C. make capacity
5 A 129 V dc resistive (30,000 operations)
D.C. break capacity
0.5 A 50 V dc L/R 40 ms (30,000 operations)
200 mA 129 V dc L/R 40 ms (30,000 operations)

ISOLATION

2 kV RMS for 1 minute output to frame
1 kV RMS for 1 minute across open contact

TRANSIENT PROTECTION

IEEE C37.90.1
IEC 60255 Class 3

Impulse Voltage Withstand

Common mode 5 kV (output to frame)

Across output contact 1 kV

High Frequency Disturbance

Common mode 2.5 kV (output to frame)

Fast Transient (IEC 61000-4-4)

4 kV 5 kHz capacitively coupled
2 kV 5 kHz direct injection

PRODUCT SAFETY

This product complies with the U.S. Standard for Safety UL 61010-1 - Safety requirements for electrical equipment for measurement, control, and laboratory use - PART 1: GENERAL REQUIREMENTS - Edition 2 - Revision Date 2008/10/28 and CSA C22.2 NO. 61010-1 - Safety requirements for Electrical equipment for measurement, control, and laboratory use.

20 CHANNEL ANALOG INPUT MODULE (ISOLATED) FUNCTIONAL SPECIFICATIONS

20 Channel Analog Module (1 kV Isolated)

20 Analog Input

NUMBER OF CHANNELS

20 Analog field inputs
2 Internal check analog inputs

ANALOG INPUTS

Input Circuit

20 separately isolated analog inputs

Analog-to-digital Converter Type

Sigma Delta

Resolution

12 bits plus sign

Input Update Rate (Data Age)

<600 ms includes calibration cycle

Input Signal Range

±2 V dc

Input Signal Scaling

Current loop resistor

Full Scale Range

±4000 counts (over range ±4095 counts)

Maximum Error at 25°C

±0.1% full scale

Common Mode Error

0.0001% per Volt to a maximum of 1000 V ac (120 dB)

Temperature Error

0.002% per °C

Maximum Error Over Temperature and Common Mode Range

±0.25% full scale

Differential Mode Rejection

60 dB minimum at 60 Hz

Differential Mode Voltage Without Damage

±24 V dc or peak ac

Common Mode Rejection

120 dB at 1000 V ac, dc to 60 Hz balanced input

20 CHANNEL ANALOG INPUT MODULE (ISOLATED) FUNCTIONAL SPECIFICATIONS(CONTINUED)

Maximum Common Mode Voltage
Operating within spec 1000 V ac RMS
Transient Protection
IEEE C37.90.1
IEC 60255 Class 3
 Impulse Voltage Withstand
 Common mode 2 kV (input to ground)
 Differential mode 0.5 kV (across input)
 High Frequency Disturbance
 Common mode 1 kV (input to ground)
 Fast Transient (IEC 61000-4-4)
 4 kV 5 kHz capacitively coupled
Reference Voltages
Auto calibration on individual channels does not require external check voltages.

20 Channel Analog Terminal Assembly

PRINTED CIRCUIT BOARD

261.8 mm x 35 mm attached to frame by

screws. Terminals sized for 1.5 mm² wire

TERMINALS

2 Terminals per point
1 chassis terminal per four input channels
Loop drop resistor mounted on rear side of terminal board.

MONITORS/INDICATORS

Green/Red RUN/FAIL LED

PRODUCT SAFETY

This product complies with the U.S. Standard for Safety UL 61010-1 - Safety requirements for electrical equipment for measurement, control, and laboratory use - PART 1: GENERAL REQUIREMENTS - Edition 2 - Revision Date 2008/10/28 and CSA C22.2 NO. 61010-1 - Safety requirements for Electrical equipment for

ANALOG/DIGITAL INPUT MODULE FUNCTIONAL SPECIFICATIONS

4 Analog/32 Digital Input Module (1 kV Isolated)

NUMBER OF CHANNELS

4 Analog field inputs
32 Status inputs

ANALOG INPUTS

Input Circuit
4 differential inputs per input module
Analog-to-Digital Converter Type
Sigma Delta
Analog-to-Digital Conversion Time
20ms
Resolution
12 bits plus sign
Input Update Rate (Data Age)
20 ms
Input Signal Range
±2 V dc
Input Signal Scaling
Dropping resistor for current inputs or voltage

Full Scale Range

±4000 counts (over range ±4095 counts)

Maximum Error at 25°C and 0 V Common Mode

±0.1% full scale

Common Mode Error

0.0001% per Volt to a maximum of 1000 V ac (120 dB)

Temperature Error

0.002% per °C over temperature range

Maximum Error Over Temperature and Common Mode Range

±0.25% full scale

Differential Mode Rejection

60 dB minimum at 50/60 Hz

Differential Mode Voltage Without Damage

±24 V dc or peak ac

Common Mode Rejection

120 dB at 1000 Vac, dc to 60 Hz balanced input

Maximum Common Mode Voltage

Operating within spec 1000 V ac

ANALOG/DIGITAL INPUT MODULE FUNCTIONAL SPECIFICATIONS (CONTINUED)

ANALOG INPUTS (CONT.)

Reference Voltages

Auto Calibration on individual channels does not require external check voltages

Transient Protection

IEEE C37.90.1

IEC 60255 Class 2

Impulse Voltage Withstand

Common mode 2 kV (input to ground)

Differential mode 1 kV (across input)

High Frequency Disturbance

Common mode 1 kV (input to ground)

Differential mode 0.5 kV (across input)

Fast Transient (IEC 61000-4-4)

4 kV 5 kHz capacitively coupled

DIGITAL INPUTS

Input Circuits

32 per input module in 4 groups of 8 inputs

Input Types

Any input can be used as: Status, Momentary Change Detect, Sequence of Events, Accumulator (1 or 2 inputs per accumulator)

Circuit Types

Common return per group of 8 inputs

Common positive or common negative

Input Voltage

24 V to 129 V, selected individually per input by jumper setting; factory default range is 48-129 V; field configurable to 24-48 V.

Input Current

5 mA per input (nominal)

Isolation Type

Opto-coupler

Insulation

2 kV RMS for 1 minute input to frame (ground)

Transient Protection

IEEE C37.90.1

IEC 60255 Class 3

Impulse Voltage Withstand

Common mode 5 kV (input to frame)

Differential mode 5 kV (input to common)

High Frequency Disturbance

Common mode 2.5 kV (input to ground)

Differential mode 1 kV (input to common)

Fast Transient (IEC 61000-4-4)

4 kV 5 kHz capacitively coupled
2 kV 5 kHz direct injection

PRODUCT SAFETY

This product complies with the U.S. Standard for Safety UL 61010-1 - Safety requirements for electrical equipment for measurement, control, and laboratory use - PART 1: GENERAL

REQUIREMENTS - Edition 2 - Revision Date

2008/10/28 and CSA C22.2 NO. 61010-1 - Safety requirements for Electrical equipment for measurement, control, and laboratory use.

12 CHANNEL DIGITAL OUTPUT MODULES FUNCTIONAL SPECIFICATIONS

12 Channel Digital Output Modules

Pilot or Magnetically Latched Relay

NUMBER OF CHANNELS

Twelve

OUTPUT TYPES

Outputs can be configured as: Level, Pulse, Trip/Close (in pairs), Raise/Lower (in pairs), Latching

SECURITY

One or more than one relay energized test

Pilot Relay Output Module

NUMBER OF RELAYS

Twelve

RELAY COIL CURRENT

27 mA

CONTACT ARRANGEMENT

Two-pole N/O relays with contacts connected in series to boost dc rating (output is single pole)

CONTACT RATING

5 A 250 V ac $\cos \phi = 0.4$ (30,000 operations)

D.C. make capacity

5 A 129 V dc (30,000 operations)

D.C. break capacity

1 A 50 V dc L/R 40 ms (30,000 operations)

200 mA 129 V dc L/R 40 ms (30,000

operations)

ISOLATION

2 kV RMS for 1 minute output to frame

1 kV RMS for 1 minute across open contact

2 kV RMS for 1 minute between outputs

TRANSIENT PROTECTION

IEEE C37.90.1

IEC 60255 Class 3

Impulse Voltage Withstand

Common mode 5 kV (output to frame)

Across output contact 2.5 kV

High Frequency Disturbance

Common mode 2.5 kV (output to frame)

Between outputs 2.5 kV

Fast Transient (IEC 61000-4-4)

4 kV 5 kHz capacitively coupled

2 kV 5 kHz direct injection

Magnetically Latched Relay Output Module

NUMBER OF RELAYS

Twelve

RELAY TYPE

Latching

RELAY COIL CURRENT

27 mA while latching

CONTACT ARRANGEMENT

Two-pole N/O relays with contacts connected in series to boost dc rating (output is single pole)

CONTACT RATING

5 A 250 V ac $\cos \phi = 0.4$ (30,000 operations)

D.C. make capacity

5 A 129 V dc (30,000 operations)

D.C. break capacity

1 A 50 V dc L/R 40 ms (30,000 operations)

200 mA 129 V dc L/R 40 ms (30,000

operations)

ISOLATION

2 kV RMS for 1 minute output to frame

1 kV RMS for 1 minute across open contact

2 kV RMS for 1 minute between outputs

TRANSIENT PROTECTION

IEEE C37.90.1

IEC 60255 Class 3

Impulse Voltage Withstand

Common mode 5 kV (output to frame)

Across open contact 2.5 kV

High Frequency Disturbance

Common mode 2.5 kV (output to frame)

Between outputs 2.5 kV

Fast Transient (IEC 61000-4-4)

4 kV 5 kHz capacitively coupled

2 kV 5 kHz direct injection

Control Output Termination Assembly

Printed circuit board 261.8 mm x 35 mm attached to frame by screws

TERMINALS

Two terminals per relay. Terminals sized for 1.5 mm² wire.

MONITORS/INDICATORS

Green/Red RUN/FAIL LED

8 CHANNEL DIGITAL OUTPUT MODULES FUNCTIONAL SPECIFICATIONS

8 Channel Digital Output 10A Module

Heavy Duty non-latched Relay

NUMBER OF CHANNELS

Eight

OUTPUT TYPES

Outputs can be configured as: Level, Pulse, Trip/Close (in pairs), Raise/Lower (in pairs), Latching

SECURITY

One or more than one relay energized test

NUMBER OF RELAYS

Sixteen single pole N/O relays with contacts connected in series to boost dc rating

RELAY COIL CURRENT

75 mA for two coils associated with each output

CONTACT ARRANGEMENT

Output is single pole normally open

CONTACT RATING

10 A 130 V ac cos ϕ = 0.4 (30,000 operations)
10 A 150 V dc resistive (30,000 operations)
5 A 150 V dc L/R 40 ms (30,000 operations)

ISOLATION

2 kV rms for 1 minute output to frame
1 kV rms for 1 minute across open contact
2 kV rms for 1 minute between outputs

TRANSIENT PROTECTION

IEEE C37.90.1
IEC 60255 Class 3
Impulse Voltage Withstand
Common mode 5 KV (output to frame)
Between outputs 5 KV
High Frequency Disturbance
Common mode 2.5 KV (output to frame)
Between outputs 2.5 KV
Fast Transient (IEC 61000-4-4)
4 KV 5 kHz capacitively coupled
2 KV 5 kHz direct injection

CONTROL OUTPUT TERMINATION ASSEMBLY

Printed circuit board 261.8 mm x 35 mm
attached to frame by screws

TERMINALS

Two terminals per relay. Plastic encased wire loop screw terminals sized for 2.5 mm² (16 AWG) wire.

MONITORS/INDICATORS

Green/Red RUN/FAIL LED

4 CHANNEL ANALOG OUTPUT MODULE FUNCTIONAL SPECIFICATIONS

4 Channel Analog Output Module

CHANNELS

Four

OUTPUTS

Each output is configurable:

Range	Counts	Output Steps
4 to 20 mA	0 to 4000	4000
4 to 20 mA	800 to 4000	3200
0 to 10 mA	0 to 4000	2560
0 to 16 mA	0 to 4000	4000
4 to 20 mA	0 to 2000	2000
4 to 20 mA	400 to 2000	1600
0 to 10 mA	0 to 2000	1280
0 to 16 mA	0 to 2000	2000

NOTE

Where the count range is greater than the number of output steps, some changes in counts may not result in a corresponding step change.

ACCURACY (4 TO 20 MA)

±0.1% full scale at 25°C

±0.25% full scale over temperature range

ACCURACY (0 TO 16 MA)

±1% full scale over temperature range

EXTERNAL LOOP POWER

24 V (maximum 36 V, minimum 19 V)

LOOP LOAD RESISTANCE

0 ohms minimum, 600 ohms maximum

TRANSIENT PROTECTION

IEEE C37.90.1

IEC 60255 Class 3

Impulse Voltage Withstand

Common mode 5 kV (output to frame)

Across open contact 2.5 kV

High Frequency Disturbance

Common mode 2.5 kV (output to frame)

Between outputs 2.5 kV

Fast Transient (IEC 61000-4-4)

4 kV 5 kHz capacitively coupled

CHANNEL ISOLATION

50 V dc channel to chassis

50 V dc channel to channel

4 Channel Analog Output Termination

Assembly

261.8 mm x 35 mm attached to frame by screws

TERMINALS

Four terminal blocks

Terminal 1	+ Loop power
Terminal 2	Loop power common
Terminal 3	+I (current out)
Terminal 4	-I (current return)

MONITORS/INDICATORS

Green/Red RUN/FAIL LED

PRODUCT SAFETY

This product complies with the U.S. Standard for Safety UL 61010-1 - Safety requirements for electrical equipment for measurement, control, and laboratory use - PART 1: GENERAL

REQUIREMENTS - Edition 2 - Revision Date

2008/10/28 and CSA C22.2 NO. 61010-1 - Safety requirements for Electrical equipment for measurement, control, and laboratory use.

PHYSICAL SPECIFICATIONS

SCD5200 Input/Output Modules share the same physical and environmental specifications.

Physical Size

Each plug-in module requires frame space of 35 mm. Modules are assemblies of one or more printed circuit boards. These modules plug into a backplane

(Electrobus) via a DIN 41612 connector and are double Eurocard size (233.4 mm x 149 mm). DIN 41612 connectors are also fitted to the front edge of the PCB to provide connection to the terminal board assembly.

ENVIRONMENTAL SPECIFICATIONS

Operating Temperature

STANDARD

0°C to +60°C (32°F to 140°F)

Humidity

10 to 95% (non-condensing)

ORDERING INFORMATION

Part Number	Description
Multiple I/O Modules	
SY-0399095	SCD5200 Multi Input Output Module 129 V 8 Mini Pilot Relay
SY-0399094	SCD5200 Multi Input Output Module 48 V 8 Mini Pilot Relay
SY-0399088	SCD5200 Multi Input Output Module 24 V 8 Mini Pilot Relay
SY-0399097	SCD5200 Multi Input Output Module 129 V 6 Paired Pilot Relay
SY-0399096	SCD5200 Multi Input Output Module 48 V 6 Paired Pilot Relay
SY-0399089	SCD5200 Multi Input Output Module 24 V 6 Paired Pilot Relay
Analog Input Module	
SY-0399085	SCD5200 20 Channel Analog Input Module (Isolated)
Analog/Digital Input Module	
SY-0399160	SCD5200 4 Analog/32 Digital Input Module (24 V to 129 V)
SY-0399222	SCD5200 4 Isolated Analog Inputs and 32 Digital Inputs (Deep Wiring Channel) Module
Digital Output Modules	
SY-0399086	SCD5200 12 Pilot Relay Digital Output Module
SY-0399087	SCD5200 12 Magnetically Latched Relay Digital Output Module
SY-0399136	SCD5200 8 Digital Output 10 Amp Module
Analog Output Module	
SY-0399084	SCD5200 4 Channel Analog Output Module

PSS 31H-8G2

Page 18

Foxboro®

by Schneider Electric

Invensys Systems, Inc.
38 Neponset Avenue
Foxborough, MA 02035-2037
United States of America
www.schneider-electric.com

Global Customer Support
Inside U.S.: 1-866-746-6477
Outside U.S.: 1-508-549-2424
Website: <https://support.ips.invensys.com>

Copyright 2014-2016 Invensys Systems, Inc.
All rights reserved.
Invensys is now part of Schneider Electric.

Schneider Electric, Invensys, Foxboro, and Foxboro Evo
are trademarks owned by Schneider Electric S.E, its
subsidiaries and affiliates.
All other trademarks are the property of their respective
owners.

MB 031

0316